

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0022027133

Status:

Active

Overview:

KK® Interconnect System - Molex

Description:

KK® 254 PC Board Connector, Top Entry, with Cat Ear Terminal, 2.54µm Tin (Sn), 13 Circuits, without Hooks

Documents:

3D Model

Drawing (PDF)

Product Specification PS-10-07-001 (PDF)

RoHS Certificate of Compliance (PDF)

Agency Certification

CSA

LR19980

UL

E29179

General

Product Family

Series

Application

Overview

Product Name

UPC

PCB Receptacles

4455

Board-to-Board, Signal

KK® Interconnect System - Molex

KK® 254

800754915717

Physical

Circuits (Loaded)

Circuits (maximum)

Color - Resin

Flammability

Glow-Wire Compliant

Guide to Mating Part

Keying to Mating Part

Lock to Mating Part

Material - Metal

Material - Plating Mating

Material - Plating Termination

Material - Resin

Net Weight

Number of Rows

Orientation

PC Tail Length

PCB Locator

PCB Retention

PCB Thickness - Recommended

Packaging Type

Pitch - Mating Interface

Pitch - Termination Interface

Plating min - Mating

Plating min - Termination

Polarized to PCB

Surface Mount Compatible (SMC)

Temperature Range - Operating

Termination Interface: Style

13

13

Natural (White)

94V-0

No

No

None

No

Brass

Tin

Tin

Nylon

1.360/g

1

Vertical

3.35mm

No

None

1.60mm

Tray

2.54mm

2.54mm

2.540µm

2.540µm

No

No

See Product Specification

Through Hole

Electrical

Current - Maximum per Contact

Grounding to PCB

Voltage - Maximum

2.5A

No

500V

Solder Process Data



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

China RoHS

REACH SVHC

Not Contained Per -
ED/30/2017 (7 July
2017)

Halogen-Free

Status

Low-Halogen

Need more information on product
environmental compliance?

Email productcompliance@molex.com
Please visit the [Contact Us](#) section for any
non-product compliance questions.

China ROHS

ELV

RoHS Phthalates

Green Image

Not Relevant

Not Contained

Search Parts in this Series

4455 Series

Mates With

KK® Header 4094 , 42376 , 42375 , 42377
, 171856 , 171857
SL™ Insulation
Displacement Connector 70475

Duration at Max. Process Temperature (seconds)	005
Lead-freeProcess Capability	WAVE
Max. Cycles at Max. Process Temperature	001
Process Temperature max. C	235
Material Info	
Engineering Number	A-4455-CY13A(P909)
Reference - Drawing Numbers	
Product Specification	PS-10-07-001
Sales Drawing	SDA-4455, SDA-4455-002

This document was generated on 07/27/2017

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION