

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: 0010894083
Status: Active
Overview: C-Grid® Products
Description: 2.54mm Pitch C-Grid® Breakaway Header, High Profile, Dual Row, Right Angle, 8 Circuits, 8.13mm Mating Pin Length, 0.38µm Gold (Au) Selective Plating

Documents:
[Drawing \(PDF\)](#)
[Product Specification PS-70216-001 \(PDF\)](#)
[Product Specification TS-70541-001-001 \(PDF\)](#)
[RoHS Certificate of Compliance \(PDF\)](#)


Agency Certification
CSA LR19980
UL E29179

General
Product Family PCB Headers
Series 70216
Application Board-to-Board, Signal, Wire-to-Board
Overview C-Grid® Products
Product Name C-Grid®
UPC 800755017762

Physical
Breakaway Yes
Circuits (Loaded) 8
Circuits (maximum) 8
Color - Resin Black
Durability (mating cycles max) 50
Flammability 94V-0
Glow-Wire Compliant No
Lock to Mating Part None
Material - Metal Brass, Phosphor Bronze
Material - Plating Mating Gold
Material - Plating Termination Tin
Material - Resin Polyester
Net Weight 0.709/g
Number of Rows 2
Orientation Right Angle
PC Tail Length 2.79mm
PCB Locator No
PCB Retention None
Packaging Type Tube
Pitch - Mating Interface 2.54mm
Plating min - Mating 3.810µm
Plating min - Termination 3.810µm
Polarized to Mating Part No
Polarized to PCB No
Shrouded No
Stackable Yes
Temperature Range - Operating -40°C to +105°C
Termination Interface: Style Through Hole

Electrical
Current - Maximum per Contact 3.0A
Voltage - Maximum 250V

Solder Process Data
Duration at Max. Process Temperature (seconds) 005



Series image - Reference only

EU ELV
Not Relevant

EU RoHS **China RoHS**
Compliant
REACH SVHC
Not Contained Per
-ED/01/2017 (12
January 2017)
Halogen-Free
Status
Not Low-Halogen

Need more information on product environmental compliance?

Email productcompliance@molex.com
Please visit the [Contact Us](#) section for any non-product compliance questions.

China ROHS Green Image
ELV Not Relevant
RoHS Phthalates Not Contained

Search Parts in this Series
70216 Series

Lead-free	Process Capability	WAVE
Max. Cycles at Max. Process Temperature		001
Process Temperature max. C		235
Material Info		
Engineering Number		70216-0276
Reference - Drawing Numbers		
Product Specification		PS-70216-001, TS-70541-001-001
Sales Drawing		SD-70216-001, SD-70216-001-002

This document was generated on 08/01/2017

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION