

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [5047541520](#)
Status: **Active**
Overview: FFC-FPC (SMT)
Description: 0.30mm Pitch Easy-On™ BackFlip™ Type FPC Connector, LA75 Series, Right Angle, Surface Mount, Dual Contact Style, 0.75mm Height, 15 Circuits

Documents:

[3D Model](#) [Packaging Specification 5047549200-200 \(PDF\)](#)
[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)
[Product Specification PS-504754-002-001 \(PDF\)](#)

General

Product Family FFC/FPC Connectors
 Series [504754](#)
 Overview [FFC-FPC \(SMT\)](#)
 Product Name BackFlip™, Easy-On™
 UPC 887191596631

Physical

Circuits (Loaded) 15
 Circuits (maximum) 15
 Color - Resin Black
 Contact Position Dual
 Durability (mating cycles max) 10
 Entry Angle 90° Angle
 Mated Height 0.75mm
 Material - Metal Copper Alloy
 Material - Plating Mating Gold
 Material - Plating Termination Gold
 Material - Resin Liquid Crystal Polymer
 Net Weight 20.999/mg
 Number of Rows 1
 Orientation Right Angle
 PCB Locator No
 PCB Retention None
 Packaging Type Embossed Tape on Reel
 Pitch - Mating Interface 0.30mm
 Pitch - Termination Interface 0.30mm
 Polarized to PCB Yes
 Stackable No
 Temperature Range - Operating -40°C to +105°C
 Termination Interface: Style Surface Mount
 Wire/Cable Type FPC only


Electrical

Current - Maximum per Contact 0.2A
 Voltage - Maximum 50V AC (RMS)/DC

Material Info

Reference - Drawing Numbers

Packaging Specification [5047549200-200](#)
 Product Specification [PS-504754-002-001](#)
 Sales Drawing [SD-504754-003](#), [SD-504754-004](#)



EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
 ED/30/2017 (7 July
 2017)

Halogen-Free

Status

Low-Halogen

**Need more information on product
 environmental compliance?**

Email productcompliance@molex.com
 Please visit the [Contact Us](#) section for any
 non-product compliance questions.

China ROHS	Green Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series

[504754 Series](#)

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION