

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** **0901220138**  
**Status:** **Active**  
**Overview:** C-Grid III™  
**Description:** 2.54mm Pitch C-Grid III™ Header, Dual Row, Right Angle, 36 Circuits, 4µm Tin (Sn) over Nickel (Ni)

**Documents:**

[3D Model](#) [Packaging Specification PK-90120-100 \(PDF\)](#)  
[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)  
[Product Specification PS-99020-0001-001 \(PDF\)](#)

**Agency Certification**

UL E29179

**General**


Product Family PCB Headers  
Series 90122  
Application Signal, Wire-to-Board  
Overview C-Grid III™  
Product Name C-Grid III™  
UPC 800753709942

**Physical**

Breakaway Yes  
Circuits (Loaded) 36  
Circuits (maximum) 36  
Color - Resin Black  
First Mate / Last Break No  
Flammability 94V-0  
Glow-Wire Compliant No  
Guide to Mating Part No  
Keying to Mating Part None  
Lock to Mating Part None  
Material - Metal Brass  
Material - Plating Mating Tin  
Material - Plating Termination Tin  
Material - Resin Polyester  
Net Weight 2.988/g  
Number of Rows 2  
Orientation Right Angle  
PC Tail Length 2.90mm  
PCB Locator No  
PCB Retention None  
Packaging Type Tray  
Pitch - Mating Interface 2.54mm  
Pitch - Termination Interface 2.54mm  
Plating min - Mating 3.048µm  
Plating min - Termination 3.048µm  
Polarized to Mating Part No  
Polarized to PCB No  
Shrouded No  
Stackable No  
Temperature Range - Operating -55°C to +125°C  
Termination Interface: Style Through Hole

**Electrical**

Current - Maximum per Contact 3.0A



Series image - Reference only

**EU ELV**

**Not Relevant**

**EU RoHS**

**Compliant**

**REACH SVHC**

Not Contained Per -  
ED/30/2017 (7 July  
2017)

**Halogen-Free**

**Status**

**Not Low-Halogen**

**Need more information on product  
environmental compliance?**

Email [productcompliance@molex.com](mailto:productcompliance@molex.com)  
Please visit the [Contact Us](#) section for any  
non-product compliance questions.

China ROHS

ELV

RoHS Phthalates

Green Image

Not Relevant

Not Contained

**Search Parts in this Series**

90122 Series

Voltage - Maximum	350V
<b>Solder Process Data</b>	
Lead-freeProcess Capability	WAVE
<b>Material Info</b>	
<b>Reference - Drawing Numbers</b>	
Packaging Specification	PK-90120-100
Product Specification	PS-99020-0001-001
Sales Drawing	SDA-90122

This document was generated on 08/02/2017

**PLEASE CHECK [WWW.MOLEX.COM](http://WWW.MOLEX.COM) FOR LATEST PART INFORMATION**