

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0878313220

Status:


Active

Overview:

Milli-Grid™ Connector System

Description:

2.00mm Pitch Milli-Grid™ Header, Vertical, Through Hole, Shrouded, 32 Circuits, 0.38µm Gold (Au) Plating, Center Polarization Slot, with Locking Windows, without PCB Locator, Tube



Documents:

3D Model

Packaging Specification PK-87831-001-001 (PDF)

Drawing (PDF)

RoHS Certificate of Compliance (PDF)

Product Specification PS-87831-027-001 (PDF)

Agency Certification		
CSA		LR19980
UL		E29179
General		
Product Family		PCB Headers
Series		87831
Application		Signal, Wire-to-Board
Comments		Contact Molex for application in automotive industry
Overview		Milli-Grid™ Connector System
Product Name		Milli-Grid™
UPC		822348274208
Physical		
Breakaway		No
Circuits (Loaded)		32
Circuits (maximum)		32
Color - Resin		Black
Durability (mating cycles max)		100
First Mate / Last Break		No
Flammability		94V-0
Glow-Wire Compliant		No
Guide to Mating Part		No
Keying to Mating Part		None
Lock to Mating Part		Yes
Material - Metal		Phosphor Bronze
Material - Plating Mating		Gold
Material - Plating Termination		Tin
Material - Resin		Nylon
Net Weight		1.433/g
Number of Rows		2
Orientation		Vertical
PC Tail Length		2.50mm
PCB Locator		No
PCB Retention		None
PCB Thickness - Recommended		1.60mm
Packaging Type		Tube
Pitch - Mating Interface		2.00mm
Pitch - Termination Interface		2.00mm
Plating min - Mating		0.381µm
Plating min - Termination		1.905µm
Polarized to PCB		No
Shrouded		Yes
Stackable		No
Surface Mount Compatible (SMC)		Yes

EU ELV

Not Relevant

EU RoHS

China RoHS

Compliant

REACH SVHC

Not Contained Per -

ED/30/2017 (7 July

2017)

Halogen-Free

Status

Not Low-Halogen

Need more information on product environmental compliance?

Email productcompliance@molex.com
Please visit the [Contact Us](#) section for any non-product compliance questions.

China ROHS	Green Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series

87831 Series

Mates With

Milli-Grid™ Vertical Through Hole

Receptacle 79107 , 78787 , Milli-Grid™

Flex-to-Board Vertical Receptacle 79108

, Milli-Grid™ Vertical Surface Mount

Receptacle 79109 , 78788 , Milli-Grid™

Crimp Housing 51110 , Milli-Grid™ Cable-to-

Board Receptacle 87568

Temperature Range - Operating	-55°C to +105°C
Termination Interface: Style	Through Hole
Electrical	
Current - Maximum per Contact	2.0A
Voltage - Maximum	125V
Solder Process Data	
Duration at Max. Process Temperature (seconds)	010
Lead-freeProcess Capability	WAVE
Max. Cycles at Max. Process Temperature	001
Process Temperature max. C	260
Material Info	
Reference - Drawing Numbers	
Packaging Specification	PK-87831-001-001
Product Specification	PS-87831-027-001
Sales Drawing	SD-87831-0001-001

This document was generated on 08/28/2017

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION