
This document was generated on 07/27/2017

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: 0010112093
Status: Active
Overview: KK® Interconnect System - Molex
Description: KK® 254 Crimp Housing, High Pressure, 9 Circuits



Series image - Reference only

Documents:

3D Model
Drawing (PDF)
Product Specification PS-7879-001 (PDF)
Packaging Specification PK-7880-001-001 (PDF)
RoHS Certificate of Compliance (PDF)

Agency Certification

CSA	LR19980
UL	E29179

General

Product Family	Crimp Housings
Series	7880
Application	Signal, Wire-to-Board
Overview	KK® Interconnect System - Molex
Product Name	KK® 254
UPC	800754241434

Physical

Circuits (maximum)	9
Color - Resin	Natural (White)
Flammability	94V-0
Gender	Receptacle
Glow-Wire Compliant	No
Material - Resin	Nylon
Net Weight	0.882/g
Number of Rows	1
Packaging Type	Bag
Panel Mount	No
Pitch - Mating Interface	2.54mm
Pitch - Termination Interface	2.54mm
Stackable	No
Temperature Range - Operating	See Product Specification

Solder Process Data

Lead-freeProcess Capability	N/A

Material Info

Engineering Number	7880-09B

Reference - Drawing Numbers

Packaging Specification	PK-7880-001-001
Product Specification	PS-7879-001
Sales Drawing	SD-7880

EU ELV
Not Relevant

EU RoHS
Compliant

China RoHS

REACH SVHC
Not Contained Per - ED/30/2017 (7 July 2017)

Halogen-Free Status
Low-Halogen

Need more information on product environmental compliance?

Email productcompliance@molex.com
Please visit the Contact Us section for any non-product compliance questions.

China ROHS	Green Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series
7880 Series

Mates With
KK®254 PCB Headers 42375 , 42377 , 42376 , 4030 , 6373 , 6410

Use With
7879 KK® High Pressure Crimp Terminal

This document was generated on 07/27/2017

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION