

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: **0464371003**
Status: **Active**
Overview: EXTreme Ten60Power™ High-Current Connector
Description: 2.54mm, 5.50mm Pitch EXTreme Ten60Power™ Right Angle Plug Assembly with Guide Pins, 24 Signal Circuits, 6 Power Circuits

Documents:

[Drawing \(PDF\)](#) [Packaging Specification PK-46437-001-001 \(PDF\)](#)
[Product Specification PS-46436-100-001 \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)
[Application Specification AS-46436-100-001 \(PDF\)](#)

Agency Certification


CSA LR19980
 UL E29179

General

Product Family PCB Headers
 Series 46437
 Application Board-to-Board, Power, Signal
 Comments See PS-46436-100 for details
 Overview [EXTreme Ten60Power™ High-Current Connector](#)
 Product Name EXTreme Ten60Power™
 UPC 800756953847

Physical

(p)ower-(s)ignal Configuration 6p - 24s
 Breakaway No
 Circuits (Loaded) 30
 Circuits (maximum) 30
 Color - Resin Black
 Durability (mating cycles max) 200
 First Mate / Last Break No
 Flammability 94V-0
 Glow-Wire Compliant No
 Guide to Mating Part Yes
 Keying to Mating Part None
 Lock to Mating Part No
 Mated Height 18.00mm
 Material - Metal Copper
 Material - Plating Mating Gold
 Material - Plating Termination Tin
 Material - Resin High Temperature Thermoplastic
 Net Weight 23.629/g
 Number of Rows 1, 3
 Orientation Right Angle
 PC Tail Length 2.84mm
 PCB Locator Yes
 PCB Retention None
 PCB Thickness - Recommended 1.58mm
 Packaging Type Tray
 Pitch - Mating Interface 2.54mm, 5.50mm
 Polarized to Mating Part Yes
 Polarized to PCB Yes
 Shrouded No
 Stackable No
 Surface Mount Compatible (SMC) No
 Temperature Range - Operating -40°C to +105°C



EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per
 -ED/01/2017 (12
 January 2017)

Halogen-Free

Status

Low-Halogen

Need more information on product environmental compliance?

Email productcompliance@molex.com
 Please visit the [Contact Us](#) section for any non-product compliance questions.

China ROHS

ELV

RoHS Phthalates

China RoHS

Green Image

Not Relevant

Not Contained

Search Parts in this Series

[46437](#) Series

Mates With

[46562-1003](#) EXTreme Ten60Power™
 Vertical Receptacle, [46436-1003](#) EXTreme
 Ten60Power™ Right Angle Receptacle

Termination Interface: Style	Through Hole
Electrical	
Current - Maximum per Contact	2.5A, 60.0A
Voltage - Maximum	600V AC / 250V DC
Solder Process Data	
Duration at Max. Process Temperature (seconds)	040
Lead-free Process Capability	SMC&WAVE
Max. Cycles at Max. Process Temperature	003
Process Temperature max. C	260
Material Info	
Reference - Drawing Numbers	
Application Specification	AS-46436-100-001
Packaging Specification	PK-46437-001-001
Product Specification	PS-46436-100-001
Sales Drawing	SD-46437-103

This document was generated on 06/30/2017

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION