

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [0459110012](#)  
**Status:** **Active**  
**Overview:** Edge Card Connectors  
**Description:** EXTreme PowerEdge™, Mixed Power/Signal Card Edge Connector, Double Sided, 3 Segments or 3.18mm Thick PC Board

**Documents:**

[3D Model](#) [Packaging Specification PK-45714-001 \(PDF\)](#)  
[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

**Agency Certification**

CSA LR19980  
 UL E29179

**General**

Product Family Edge Card Connectors  
 Series [45911](#)  
 Circuit Size Range 1-64 Circuits  
 Component Type Edgcard to PCB  
 Data Rate Unrated  
 Edge Card Thickness 1.57mm  
 High Power Bay (30.0A or more) Yes  
 Orientation Vertical  
 Overview [Edge Card Connectors](#)  
 Product Name EXTreme PowerEdge™  
 Standard Based General  
 UPC 822350702027

**Physical**


(p)ower-(s)ignal Configuration 8s - 2p - 2p  
 Circuits (Loaded) 12  
 Circuits (maximum) 12  
 Color - Resin Black  
 Durability (mating cycles max) 250  
 Entry Angle Vertical (Top Entry)  
 Flammability 94V-0  
 Keying to Mating Part N/A  
 Material - Metal Phosphor Bronze  
 Material - Plating Mating Gold  
 Material - Plating Termination Tin  
 Material - Resin High Temperature Thermoplastic  
 Net Weight 6.796/g  
 PC Tail Length 4.50mm  
 PCB Thickness - Recommended 3.18mm  
 Packaging Type Tray  
 Pitch - Mating Interface 12.90mm  
 Plating min - Mating 0.762µm  
 Plating min - Termination 3.810µm  
 Temperature Range - Operating -40°C to +105°C  
 Termination Interface: Style Through Hole

**Electrical**

Current - Maximum per Contact 3.0A, 40.0A  
 Voltage - Maximum 250V

**Solder Process Data**

Duration at Max. Process Temperature (seconds) 005  
 Lead-freeProcess Capability WAVE



**EU ELV**

**Not Relevant**

**EU RoHS**

**Compliant**

**REACH SVHC**

Not Contained Per  
 -ED/01/2017 (12  
 January 2017)

**Halogen-Free**

**Status**

**Low-Halogen**

**Need more information on product environmental compliance?**

Email [productcompliance@molex.com](mailto:productcompliance@molex.com)  
 Please visit the [Contact Us](#) section for any non-product compliance questions.

China ROHS	Green Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

**Search Parts in this Series**

[45911 Series](#)

**Mates With**

1.58mm Double Sided Card Edge

Max. Cycles at Max. Process Temperature	001
Process Temperature max. C	245

**Material Info**

**Reference - Drawing Numbers**

Packaging Specification	PK-45714-001
Sales Drawing	SD-45911-001, SD-45911-002

This document was generated on 06/30/2017

**PLEASE CHECK [WWW.MOLEX.COM](http://WWW.MOLEX.COM) FOR LATEST PART INFORMATION**