

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** **0643241019**  
**Status:** **Active**  
**Overview:** CMC and CMX Sealed, Hybrid, Modular Connectors  
**Description:** 2.80mm, CMC CP Female Terminal, Tin plated, for Tab Dimensions 2.8mm x 0.8mm , Wire Size > 3mm<sup>2</sup> - 5mm<sup>2</sup>

**Documents:**

<a href="#">3D Model</a>	<a href="#">Application Specification AS-64324-001-CH-001 (PDF)</a>
<a href="#">Drawing (PDF)</a>	<a href="#">Application Specification AS-64324-001-FR-001 (PDF)</a>
<a href="#">Product Specification PS-64326-001-001 (PDF)</a>	<a href="#">Application Specification AS-98420-001-001 (PDF)</a>
<a href="#">Application Specification AS-64318-002-001 (PDF)</a>	<a href="#">Application Specification AS-98420-001-CH-001 (PDF)</a>
<a href="#">Application Specification AS-64318-002-CH-001 (PDF)</a>	<a href="#">Application Specification AS-98420-001-FR-001 (PDF)</a>
<a href="#">Application Specification AS-64318-002-FR-001 (PDF)</a>	<a href="#">Application Specification AS-98420-001-SP-001 (PDF)</a>
<a href="#">Application Specification AS-64318-002-SP-001 (PDF)</a>	<a href="#">Packaging Specification PK-98910-001-001 (PDF)</a>
<a href="#">Application Specification AS-64324-001-001 (PDF)</a>	<a href="#">RoHS Certificate of Compliance (PDF)</a>

**General**

Product Family	Crimp Terminals
Series	<b>64324</b>
Application	Power
Comments	* Current tested on a fully loaded connector, current for temperature increase of 40°C. Current max = 21A for 2.80mm Terminal (5.00mm <sup>2</sup> wire)*
Crimp Quality Equipment	Yes
Overview	<a href="#">CMC and CMX Sealed, Hybrid, Modular Connectors</a>
Product Name	CMC, CP Terminal
UPC	883906127893

**Physical**

Gender	Female
Material - Metal	High Copper
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Net Weight	1.150/g
Packaging Type	Reel
Plating min - Mating	1.016µm
Termination Interface: Style	Crimp or Compression
Wire Insulation Diameter	0.51-1.29mm
Wire Size AWG	16, 18, 20, 22, 24
Wire Size mm <sup>2</sup>	0.20-1.30

**Electrical**


Current - Maximum per Contact	21.0A
Voltage - Maximum	14V DC

**Solder Process Data**

Lead-freeProcess Capability	N/A
-----------------------------	-----

**Material Info**

**Reference - Drawing Numbers**



*Series image - Reference only*

**EU ELV**

**Compliant**

**EU RoHS**

**Compliant**

**REACH SVHC**

Not Contained Per - ED/30/2017 (7 July 2017)

**Halogen-Free**

**Status**

**Not Relevant**

**Need more information on product environmental compliance?**

Email [productcompliance@molex.com](mailto:productcompliance@molex.com)  
Please visit the [Contact Us](#) section for any non-product compliance questions.

China ROHS	Not Relevant
ELV	Compliant
RoHS Phthalates	Not Contained

**Search Parts in this Series**

[64324 Series](#)

**Mates With**

CMC Connector [64318](#) , [64321](#) , [64326](#) , [64325-1196](#)

**Use With**

CMC Connector [64318](#) , [64321](#) , [64326](#) , [64325-1196](#)

Application Specification

AS-64318-002-001, AS-64318-002-CH-001,  
AS-64318-002-FR-001, AS-64318-002-SP-001,  
AS-64324-001-001, AS-64324-001-CH-001,  
AS-64324-001-FR-001, AS-98420-001-001,  
AS-98420-001-CH-001, AS-98420-001-FR-001,  
AS-98420-001-SP-001

Packaging Specification

PK-98910-001-001

Product Specification

PS-64326-001-001

Sales Drawing

SD-64324-001

This document was generated on 09/08/2017

**PLEASE CHECK [WWW.MOLEX.COM](http://WWW.MOLEX.COM) FOR LATEST PART INFORMATION**