

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [0346909200](#)  
**Status:** **Active**  
**Overview:** Stac64™ Single, Multi-Pocket and Hybrid Header System  
**Description:** Stac64™ Vertical Header Assembly, 20 Circuits, Polarization A, Black, Tube

**Documents:**

<a href="#">3D Model</a>	<a href="#">Packaging Specification PK-31301-063 (PDF)</a>
<a href="#">Drawing (PDF)</a>	<a href="#">RoHS Certificate of Compliance (PDF)</a>
<a href="#">Product Specification PS-34729-020-001 (PDF)</a>	<a href="#">Product Literature (PDF)</a>
<a href="#">Application Specification AS-34729-020-001 (PDF)</a>	

**General**


Product Family	PCB Headers
Series	<a href="#">34690</a>
Application	Power, Wire-to-Board
Comments	Polarization A
Overview	<u>Stac64™ Single, Multi-Pocket and Hybrid Header System</u>
Product Literature Order No	987650-4561
Product Name	Stac64™
UPC	883906211615

**Physical**

Breakaway	No
Circuits (Loaded)	20
Circuits (maximum)	20
Color - Resin	Black
Durability (mating cycles max)	10
First Mate / Last Break	No
Glow-Wire Compliant	No
Guide to Mating Part	No
Keying to Mating Part	None
Lock to Mating Part	Yes
Material - Metal	Brass
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Material - Resin	High Temperature Thermoplastic
Net Weight	7.555/g
Number of Rows	2
Orientation	Vertical
PC Tail Length	3.33mm
PCB Locator	Yes
PCB Retention	None
PCB Thickness - Recommended	1.57mm
Packaging Type	Tube
Pitch - Mating Interface	2.54mm
Pitch - Termination Interface	2.54mm
Polarized to Mating Part	Yes
Polarized to PCB	Yes
Shrouded	Yes
Stackable	No
Surface Mount Compatible (SMC)	No
Temperature Range - Operating	-40°C to +100°C
Termination Interface: Style	Through Hole

**Electrical**

Current - Maximum per Contact	10.0A
-------------------------------	-------



**EU ELV**

**Compliant**

**EU RoHS**

**Compliant**

**China RoHS**

**REACH SVHC**

Not Contained Per  
-ED/01/2017 (12  
January 2017)

**Halogen-Free**

**Status**

**Not Relevant**

**Need more information on product environmental compliance?**

Email [productcompliance@molex.com](mailto:productcompliance@molex.com)  
Please visit the [Contact Us](#) section for any non-product compliance questions.

China ROHS	Not Relevant
ELV	Compliant
RoHS Phthalates	Not Contained

**Search Parts in this Series**

[34690 Series](#)

**Mates With**

[34729](#) 2.54mm (.100") Pitch Stac64™ Right Angle Receptacle, [31408](#) USCAR 2.54mm (.100") Pitch Receptacle

Voltage - Maximum 500V

**Solder Process Data**

Duration at Max. Process Temperature (seconds) 040  
Lead-free Process Capability WAVE  
Max. Cycles at Max. Process Temperature 003  
Process Temperature max. C 260

**Material Info**

**Reference - Drawing Numbers**

Application Specification AS-34729-020-001  
Packaging Specification PK-31301-063  
Product Specification PS-34729-020-001  
Sales Drawing SD-34707-200, SD-34707-300, SD-34707-400

This document was generated on 09/04/2017

**PLEASE CHECK [WWW.MOLEX.COM](http://WWW.MOLEX.COM) FOR LATEST PART INFORMATION**