

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0347290162](#)
Status: **Active**
Overview: [Stac64™ Single, Multi-Pocket and Hybrid Header System](#)
Description: [Stac64™ Receptacle Assembly, 16 Circuits, Polarization C, Brown, Tray](#)

Documents:

3D Model	Packaging Specification PK-31301-201 (PDF)
Drawing (PDF)	RoHS Certificate of Compliance (PDF)
Product Specification PS-34729-020-001 (PDF)	Product Literature (PDF)
Application Specification AS-34729-020-001 (PDF)	

General


Product Family	PCB Receptacles
Series	34729
Application	Signal, Wire-to-Board
Comments	Polarization C
Overview	Stac64™ Single, Multi-Pocket and Hybrid Header System
Product Literature Order No	987650-4561
Product Name	Stac64™
UPC	884982006607

Physical

Circuits (Loaded)	16
Circuits (maximum)	16
Color - Resin	Brown
Durability (mating cycles max)	10
Glow-Wire Compliant	No
Guide to Mating Part	No
Keying to Mating Part	None
Lock to Mating Part	Yes
Material - Metal	Brass
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Material - Resin	High Temperature Thermoplastic
Net Weight	6.420/g
Number of Rows	2
Orientation	Vertical
PC Tail Length	3.33mm
PCB Locator	Yes
PCB Retention	None
PCB Thickness - Recommended	1.60mm
Packaging Type	Tray
Pitch - Mating Interface	2.54mm
Pitch - Termination Interface	2.54mm
Polarized to Mating Part	Yes
Polarized to PCB	Yes
Robotic Placement	None
Stackable	Yes
Surface Mount Compatible (SMC)	No
Temperature Range - Operating	-40°C to +100°C
Termination Interface: Style	Through Hole

Electrical

Current - Maximum per Contact	10.0A
Voltage - Maximum	500V



Series image - Reference only

EU ELV

Compliant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
ED/30/2017 (7 July
2017)

Halogen-Free

Status

Low-Halogen

Need more information on product environmental compliance?

Email productcompliance@molex.com
Please visit the [Contact Us](#) section for any non-product compliance questions.

China ROHS	Green Image
ELV	Compliant
RoHS Phthalates	Not Contained

Search Parts in this Series

[34729](#) Series

Mates With

[34690](#) 2.54mm Pitch Stac64™ Vertical Header, [34691](#) 2.54mm Pitch Stac64™ Right Angle Header

Use With

[34803](#) CTX64 Female Terminal

Solder Process Data

Duration at Max. Process Temperature (seconds)	040
Lead-free Process Capability	SMC&WAVE
Max. Cycles at Max. Process Temperature	003
Process Temperature max. C	260

Material Info**Reference - Drawing Numbers**

Application Specification	AS-34729-020-001
Packaging Specification	PK-31301-201
Product Specification	PS-34729-020-001
Sales Drawing	SD-34729-020

This document was generated on 08/09/2017

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION