

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [5044490207](#)

Status: **Active**

Overview: [Pico-Clasp Wire-to-Board Connectors](#)

Description: 1.00mm Pitch, Pico-Clasp PCB Header, Single Row, Vertical, Surface Mount, 0.10µm Gold Plated, with Inner Friction Lock, 2 Circuits, Natural

Documents:

[3D Model \(PDF\)](#)

[3D Model](#)

[Drawing \(PDF\)](#)

[Product Specification 5013300000-PS-002 \(PDF\)](#)

[Application Specification 5013300000-AS-000 \(PDF\)](#)

[Packaging Specification SPK-504449-001-001 \(PDF\)](#)

[RoHS Certificate of Compliance \(PDF\)](#)



Series image - Reference only

General

Product Family	PCB Headers
Series	504449
3D Viewer	Yes
Application	Signal, Wire-to-Board
CURRENT-MAX-NUMERIC	1.0
Overview	Pico-Clasp Wire-to-Board Connectors
PITCH-MATING-NUMERIC	1.00
Product Name	Pico-Clasp
UPC	887191268316

Physical

Breakaway	No
Circuits (Loaded)	2
Circuits (maximum)	2
Color - Resin	Natural
Durability (mating cycles max)	30
First Mate / Last Break	No
Glow-Wire Capable	No
Guide to Mating Part	No
Keying to Mating Part	None
Lock to Mating Part	Yes
Material - Metal	Phosphor Bronze
Material - Plating Mating	Gold
Material - Plating Termination	Gold
Material - Resin	Polyamide
Net Weight	74.700/mg
Number of Rows	1
Orientation	Vertical
PCB Locator	No
PCB Retention	Yes
Packaging Type	Embossed Tape on Reel
Pitch - Mating Interface	1.00mm
Plating min - Mating	0.102µm
Plating min - Termination	0.102µm
Polarized to Mating Part	Yes
Polarized to PCB	No
Robotic Placement	Vacuum Pick-Up Tape
Shrouded	Fully
Stackable	No
Temperature Range - Operating	-40° to +85°C
Termination Interface: Style	Surface Mount

Electrical

Current - Maximum per Contact	1.0A
-------------------------------	------

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per - ED/71/2019 (16 July 2019)

Halogen-Free

Status

Not Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

China RoHS

Green Image

Not Relevant

Not Contained

Search Parts in this Series

[504449 Series](#)

Mates With

[Pico-Clasp Female Housing 501330](#)

Voltage - Maximum

50V AC (RMS)/DC

Material Info

Reference - Drawing Numbers

Application Specification

5013300000-AS-000

Packaging Specification

SPK-504449-001-001

Product Specification

5013300000-PS-002

Sales Drawing

5044490000-SD-000

This document was generated on 11/20/2019

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION