

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: **0643221039**
Status: **Active**
Overview: CMC and CMX Sealed, Hybrid, Modular Connectors
Description: 0.635mm CMC CP Female Terminal, Tin Plated, for Square 0.6mm x 0.6mm Pins, Wire Size 0.5mm²

Documents:


3D Model	Application Specification AS-64322-001-CH-001 (PDF)
Drawing (PDF)	Application Specification AS-64322-001-FR-001 (PDF)
Product Specification PS-64319-002-001 (PDF)	Application Specification AS-98420-001-001 (PDF)
Product Specification PS-64326-001-001 (PDF)	Application Specification AS-98420-001-CH-001 (PDF)
Application Specification AS-64318-002-001 (PDF)	Application Specification AS-98420-001-FR-001 (PDF)
Application Specification AS-64318-002-CH-001 (PDF)	Application Specification AS-98420-001-SP-001 (PDF)
Application Specification AS-64318-002-FR-001 (PDF)	Application Specification AS-98420-002-001 (PDF)
Application Specification AS-64318-002-SP-001 (PDF)	Application Specification AS-98420-002-CH-001 (PDF)
Application Specification AS-64319-002-001 (PDF)	Application Specification AS-98420-002-FR-001 (PDF)
Application Specification AS-64319-002-CH-001 (PDF)	Application Specification AS-98420-002-SP-001 (PDF)
Application Specification AS-64319-002-FR-001 (PDF)	Packaging Specification PK-98913-001-001 (PDF)
Application Specification AS-64319-002-SP-001 (PDF)	RoHS Certificate of Compliance (PDF)
Application Specification AS-64322-001-001 (PDF)	

General

Product Family	Crimp Terminals
Series	64322
Application	Signal
Comments	* Current tested on a 5 terminals loaded connector, current for temperature increase of 40°C. Current max = 6A for 0.635mm Terminal(0.75mm ² wire)
Crimp Quality Equipment	Yes
Overview	CMC and CMX Sealed, Hybrid, Modular Connectors
Product Name	CMC, CP Terminal
UPC	883906129491

Physical

Gender	Female
Material - Metal	Phosphor Bronze
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Net Weight	0.150/g
Packaging Type	Reel
Plating min - Mating	1.524µm, 3.048µm
Termination Interface: Style	Crimp or Compression
Wire Insulation Diameter	1.40-1.50mm
Wire Size AWG	20
Wire Size mm ²	0.50



EU ELV
Compliant

EU RoHS
Compliant
REACH SVHC

Not Contained Per -
ED/30/2017 (7 July
2017)

Halogen-Free
Status

Not Reviewed

Need more information on product environmental compliance?

Email productcompliance@molex.com
Please visit the [Contact Us](#) section for any non-product compliance questions.

China ROHS	Not Reviewed
ELV	Compliant
RoHS Phthalates	Not Contained

Search Parts in this Series
[64322](#) Series

Mates With
CMC Connector [64318](#) , [64319](#) , [64320](#) , [64321](#) , [64326](#)

Use With
CMC Connector [64318](#) , [64319](#) , [64320](#) , [64321](#) , [64326](#)

Electrical

Current - Maximum per Contact 6.0A
Voltage - Maximum 14V DC

Solder Process Data

Lead-free Process Capability N/A

Material Info**Reference - Drawing Numbers**

Application Specification AS-64318-002-001, AS-64318-002-CH-001,
AS-64318-002-FR-001, AS-64318-002-SP-001,
AS-64319-002-001, AS-64319-002-CH-001,
AS-64319-002-FR-001, AS-64319-002-SP-001,
AS-64322-001-001, AS-64322-001-CH-001,
AS-64322-001-FR-001, AS-98420-001-001,
AS-98420-001-CH-001, AS-98420-001-FR-001,
AS-98420-001-SP-001, AS-98420-002-001,
AS-98420-002-CH-001, AS-98420-002-FR-001,
AS-98420-002-SP-001
Packaging Specification PK-98913-001-001
Product Specification PS-64319-002-001, PS-64326-001-001
Sales Drawing SD-64322-001

This document was generated on 09/08/2017

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION