

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: **0901220128**
Status: **Active**
Overview: C-Grid III™
Description: 2.54mm Pitch C-Grid III™ Header, Dual Row, Right Angle, 16 Circuits, 4µm Tin (Sn) over Nickel (Ni)

Documents:

[3D Model](#) [Packaging Specification PK-90120-100 \(PDF\)](#)
[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)
[Product Specification PS-99020-0001-001 \(PDF\)](#)

Agency Certification

UL E29179


General

Product Family PCB Headers
Series [90122](#)
Application Signal, Wire-to-Board
MolexKits Yes
Overview [C-Grid III™](#)
Product Name C-Grid III™
UPC 800753710177

Physical

Breakaway Yes
Circuits (Loaded) 16
Circuits (maximum) 16
Color - Resin Black
First Mate / Last Break No
Flammability 94V-0
Glow-Wire Compliant No
Guide to Mating Part No
Keying to Mating Part None
Lock to Mating Part None
Material - Metal Brass
Material - Plating Mating Tin
Material - Plating Termination Tin
Material - Resin Polyester
Net Weight 1.328/g
Number of Rows 2
Orientation Right Angle
PC Tail Length 2.90mm
PCB Locator No
PCB Retention None
Packaging Type Tray
Pitch - Mating Interface 2.54mm
Pitch - Termination Interface 2.54mm
Plating min - Mating 3.048µm
Plating min - Termination 3.048µm
Polarized to Mating Part No
Polarized to PCB No
Shrouded No
Stackable No
Temperature Range - Operating -55°C to +125°C
Termination Interface: Style Through Hole

Electrical



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
ED/30/2017 (7 July
2017)

Halogen-Free

Status

Not Low-Halogen

**Need more information on product
environmental compliance?**

Email productcompliance@molex.com
Please visit the [Contact Us](#) section for any
non-product compliance questions.

China ROHS

ELV

RoHS Phthalates

Green Image

Not Relevant

Not Contained

Search Parts in this Series

[90122 Series](#)

Current - Maximum per Contact	3.0A
Voltage - Maximum	350V

Solder Process Data

Duration at Max. Process Temperature (seconds)	005
Lead-free Process Capability	WAVE
Max. Cycles at Max. Process Temperature	001
Process Temperature max. C	230

Material Info**Reference - Drawing Numbers**

Packaging Specification	PK-90120-100
Product Specification	PS-99020-0001-001
Sales Drawing	SDA-90122

This document was generated on 09/12/2017

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION