


PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [5019530305](#)
Status: **Active**
Overview: [Pico-Clasp Wire-to-Board Connectors](#)
Description: 1.00mm Pitch, Pico-Clasp PCB Header, Single Row, Right-Angle, Surface Mount, 0.10µm Gold Plated, with Outer Positive Lock, 3 Circuits, Natural

Documents:

Drawing (PDF)	Application Specification 5013300000-AS-000 (PDF)
3D Model	Packaging Specification 5019539200-200 (PDF)
3D Model (PDF)	RoHS Certificate of Compliance (PDF)
Product Specification 5019390000-PS-001 (PDF)	



Series image - Reference only

Agency Certification

UL E29179

General

Product Family	PCB Headers
Series	501953
3D Viewer	Yes
Application	Signal, Wire-to-Board
CURRENT-MAX-NUMERIC	1.0
Overview	Pico-Clasp Wire-to-Board Connectors
PITCH-MATING-NUMERIC	1.00
Product Name	Pico-Clasp
UPC	889056179652

Physical

Breakaway	No
Circuits (Loaded)	3
Circuits (maximum)	3
Color - Resin	Natural
Durability (mating cycles max)	30
First Mate / Last Break	No
Glow-Wire Capable	No
Guide to Mating Part	No
Keying to Mating Part	None
Lock to Mating Part	Yes
Mated Height	4.75mm
Material - Metal	Phosphor Bronze
Material - Plating Mating	Gold
Material - Plating Termination	Gold
Material - Resin	Nylon
Net Weight	112.458/mg
Number of Rows	1
Orientation	Right Angle
PCB Locator	No
PCB Retention	Yes
Packaging Type	Embossed Tape on Reel
Pitch - Mating Interface	1.00mm
Plating min - Mating	0.102µm
Plating min - Termination	0.051µm
Polarized to Mating Part	Yes
Polarized to PCB	No
Shrouded	Fully
Stackable	No
Temperature Range - Operating	-40° to +105°C
Termination Interface: Style	Surface Mount

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per - ED/71/2019 (16 July 2019)

Halogen-Free

Status

Not Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

China RoHS

Green Image

Not Relevant

Not Contained

Search Parts in this Series

[501953 Series](#)

Mates With

[Pico-Clasp Female Housing 501939](#)

Electrical

Current - Maximum per Contact
Voltage - Maximum

1.0A
50V AC (RMS)/DC

Material Info**Reference - Drawing Numbers**

Application Specification 5013300000-AS-000
Packaging Specification 5019539200-200
Product Specification 5019390000-PS-001
Sales Drawing 5019530305-SD-000, 5019530306-SD-000,
SD-501953-003-001, SD-501953-003-002,
SD-501953-004-001, SD-501953-004-002,
SD-501953-004-003

This document was generated on 11/26/2019

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION