

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [0015247180](#)  
**Status:** **Active**  
**Overview:** [Mini-Fit Products](#)  
**Description:** Mini-Fit® BMI Receptacle Header, 4.20mm Pitch, Dual Row, Vertical, with Snap-In Plastic Pegs, Post 2.54µm Tin (Sn), UL 94V-2, 18 Circuits

**Documents:**

<a href="#">3D Model</a>	<a href="#">Packaging Specification PK-42385-999 (PDF)</a>
<a href="#">Drawing (PDF)</a>	<a href="#">Test Summary 423850000-TS-000 (PDF)</a>
<a href="#">Product Specification PS-5556-002-001 (PDF)</a>	<a href="#">RoHS Certificate of Compliance (PDF)</a>
<a href="#">Product Specification TS-5556-002-001 (PDF)</a>	

**Agency Certification**

CSA	LR19980
UL	E29179

**General**

Product Family	PCB Receptacles
Series	<a href="#">42385</a>
Application	Board-to-Board, Power
Comments	Solder Type With Pegs
MolexKits	Yes
Overview	<a href="#">Mini-Fit Products</a>
Product Name	Mini-Fit® BMI
UPC	800754209526

**Physical**

Circuits (Loaded)	18
Circuits (maximum)	18
Color - Resin	Natural
Durability (mating cycles max)	30
Flammability	94V-2
Glow-Wire Compliant	No
Guide to Mating Part	Yes
Keying to Mating Part	None
Lock to Mating Part	None
Material - Metal	Brass
Material - Plating Mating	Tin
Material - Resin	Nylon
Net Weight	3.665/g
Number of Rows	2
Orientation	Vertical
PCB Locator	Yes
PCB Retention	Yes
PCB Thickness - Recommended	1.20mm
Packaging Type	Tray
Pitch - Mating Interface	4.20mm
Pitch - Termination Interface	4.20mm
Polarized to Mating Part	Yes
Polarized to PCB	Yes
Surface Mount Compatible (SMC)	No
Temperature Range - Operating	-40°C to +105°C
Termination Interface: Style	Through Hole

**Electrical**

Current - Maximum per Contact	9.0A
Grounding to PCB	No



**EU ELV**

**Not Relevant**

**EU RoHS**

**Compliant**

**REACH SVHC**

Not Contained Per - ED/30/2017 (7 July 2017)

**Halogen-Free**

**Status**

**Low-Halogen**

**Need more information on product environmental compliance?**

Email [productcompliance@molex.com](mailto:productcompliance@molex.com)  
Please visit the [Contact Us](#) section for any non-product compliance questions.

China ROHS	Green Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

**Search Parts in this Series**

[42385 Series](#)

**Mates With**

[42475](#) Panel Mount Plug, [42404](#) Right Angle Header, [42440](#) Vertical Header, [43879](#) Vertical Header, [44068](#) Vertical Header

Voltage - Maximum 600V AC (RMS)/DC

**Solder Process Data**

Duration at Max. Process Temperature (seconds) 005  
Lead-free Process Capability WAVE  
Max. Cycles at Max. Process Temperature 001  
Process Temperature max. C 240

**Material Info**

Engineering Number 42385-18A1

**Reference - Drawing Numbers**

Packaging Specification PK-42385-999  
Product Specification PS-5556-002-001, TS-5556-002-001  
Sales Drawing SDA-42385-\*  
Test Summary 423850000-TS-000

This document was generated on 07/28/2017

**PLEASE CHECK [WWW.MOLEX.COM](http://WWW.MOLEX.COM) FOR LATEST PART INFORMATION**