



Part Number : [1002973501](#)
Product Description : zQSFP+-to-zQSFP+ Cable
Assembly, 26 AWG, 5.0m Length
Series Number : 100297
Status : Active
Product Category : High-Speed I/O Cable
Assemblies



Documents & Resources

Drawings

[1002973501_sd.pdf](#)

Specifications

- [1002970003-000.pdf](#)
- [1002970004-000.pdf](#)
- [1002970006-000.pdf](#)
- [1002970007-000.pdf](#)
- [1002970008-000.pdf](#)
- [1002970009-000.pdf](#)
- [1002970020-000.pdf](#)
- [1002970021-000.pdf](#)
- [1002970023-000.pdf](#)
- [TS-100297-0004-001.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	 per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2024)4144-DC (27 June 2024)

EU RoHS	Compliant per EU 2015/863
---------	---------------------------

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

CE - Declaration of Conformity

Part Details

General

Status	Active
Category	High-Speed I/O Cable Assemblies
Series	100297
Description	zQSFP+-to-zQSFP+ Cable Assembly, 26 AWG, 5.0m Length
Assembly Configuration	Dual Ended Connectors
Connector to Connector	QSFP28-to-QSFP28, zQSFP+-to- zQSFP+
Product Name	zQSFP Plus,zQSFP+
Type	Pluggable
UPC	887191650111

Electrical

Current - Maximum per Contact	0.03A
Data Rate	28.0 Gbps
Impedance	100Ω
Voltage - Maximum	3.3V DC

Physical

Cable Bundling	None
Cable Length	5.0m
Circuits (Loaded)	38
Circuits (maximum)	38
Gender	Plug/Plug
Lock to Mating Part	Yes
Material - Metal	Zinc Die Cast
Net Weight	6716.268/g
Packaging Type	Bag
Release Style	Pull Tab
Single Ended	No
Wire/Cable Type	Round
Wire Size (AWG)	26

Mates With / Use With

Mates with Part(s)

Description	Part Number
Mates With	zQSFP Cages and Connectors