



Part Number : [151310405](#)
Product Description : Pico-Lock-to-Pico-Lock Off-the-Shelf (OTS) Cable Assembly, 1.00mm Pitch, Single Row, 450.00mm Length, 4 Circuits, Black
Series Number : 15131
Status : Active
Product Category : Power and Signal Cable Assemblies

Documents & Resources

- Drawings**
[151310405 sd.pdf](#)
- 3D Models and Design Files**
[STEP AP242](#)
[SOLIDWORKS](#)
[Creo](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	 per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2024)7663-DC (21 Jan 2025)
EU RoHS	Compliant per EU 2015/863

- [Compliance Statements](#)
- EU RoHS
 - REACH SVHC
 - Low-Halogen
- [Industry Documents](#)

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Power and Signal Cable Assemblies
Series	15131
Description	Pico-Lock-to-Pico-Lock Off-the-Shelf (OTS) Cable Assembly, 1.00mm Pitch, Single Row, 450.00mm Length, 4 Circuits, Black
Application	Signal, Wire-to-Board
Assembly Configuration	Dual Ended Connectors
Connector to Connector	Pico-Lock-to-Pico-Lock
Product Name	Pico-Lock
Type	Discrete Wire Assembly
UPC	191128284790

Electrical

Current - Maximum per Contact	2.0A
Voltage - Maximum	150V

Physical

Cable Length	450.00mm
Circuits (Loaded)	4
Circuits (maximum)	4
Color - Resin	Black
Gender	Female-Female

Lock to Mating Part	Yes
Material - Metal	Copper Alloy
Material - Plating Mating	Gold
Material - Plating Termination	Tin
Material - Resin	High Temperature Thermoplastic
Net Weight	3.044/g
Number of Rows	1
Overmolded	No
Packaging Type	Bag
Pitch - Mating Interface	1.00mm
Single Ended	No
Termination Interface Style	Crimp or Compression
Wire/Cable Type	UL 1571
Wire Size (AWG)	28

Mates With / Use With

Mates with Part(s)

Description	Part Number
1.00mm Pitch Pico-Lock Right-Angle Single Row Headers	<u>503763</u>