



**Part Number :** [1053131105](#)


**Product Description :** Nano-Fit Right-Angle Header, Through Hole, 2.50mm Pitch, Single Row, 5 Circuits, Tin (Sn) Plating, Black, Glow-Wire Capable, Tray

**Series Number :** 105313

**Status :** Active

**Product Category :** PCB Headers and Receptacles

**Packaging Alternative :** [1053131505](#) (Embossed Tape on Reel)



---

## Documents & Resources

### Drawings

[1053131105\\_sd.pdf](#)

[PK-105309-400-000.pdf](#)

### 3D Models and Design Files

[STEP AP242](#)

[SOLIDWORKS](#)

[Creo](#)

[Symbol and Footprint \(Multi-Format\)](#)

[SYM-105313-XX05-001.zip](#)

### Specifications

[AS-105300-100-001.pdf](#)

[1053001000-PS-CH-000.pdf](#)

[1053001000-PS-ES-000.pdf](#)

[1053001000-PS-JP-000.pdf](#)

[1053001000-PS-SK-000.pdf](#)

[PS-105300-100-001.pdf](#)

[1053001000-TS-000.pdf](#)

---

## Product Environment Compliance

### Compliance

|            |                                 |
|------------|---------------------------------|
| GADSL/IMDS | Compliant with Exemption 44; 33 |
|------------|---------------------------------|

|                    |                                                                                                            |
|--------------------|------------------------------------------------------------------------------------------------------------|
| China RoHS         | <br>per SJ/T 11365-2006 |
| EU ELV             | Not Relevant                                                                                               |
| Low-Halogen Status | Low-Halogen per IEC 61249-2-21                                                                             |
| REACH SVHC         | Not Contained per D(2024)7663-DC<br>(21 Jan 2025)                                                          |
| EU RoHS            | Compliant per EU 2015/863                                                                                  |

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

---

**Part Details**

**General**

|                |                                                                                                                                            |
|----------------|--------------------------------------------------------------------------------------------------------------------------------------------|
| Status         | Active                                                                                                                                     |
| Category       | PCB Headers and Receptacles                                                                                                                |
| Series         | 105313                                                                                                                                     |
| Description    | Nano-Fit Right-Angle Header,<br>Through Hole, 2.50mm Pitch, Single<br>Row, 5 Circuits, Tin (Sn) Plating,<br>Black, Glow-Wire Capable, Tray |
| Application    | Power, Wire-to-Board                                                                                                                       |
| Component Type | PCB Header                                                                                                                                 |
| Product Name   | Nano-Fit                                                                                                                                   |
| UPC            | 887191928937                                                                                                                               |

**Agency**

|     |         |
|-----|---------|
| CSA | LR19980 |
| UL  | E29179  |

## Electrical

|                               |                  |
|-------------------------------|------------------|
| Current - Maximum per Contact | 8.0A             |
| Voltage - Maximum             | 250V AC (RMS)/DC |

## Physical

|                                |                        |
|--------------------------------|------------------------|
| Breakaway                      | No                     |
| Circuits (Loaded)              | 5                      |
| Circuits (maximum)             | 5                      |
| Color - Resin                  | Black                  |
| Durability (mating cycles max) | 25                     |
| First Mate / Last Break        | No                     |
| Flammability                   | 94V-0                  |
| Glow-Wire Capable              | Yes                    |
| Guide to Mating Part           | No                     |
| Keying to Mating Part          | Yes                    |
| Lock to Mating Part            | Yes                    |
| Material - Metal               | Brass                  |
| Material - Plating Mating      | Tin                    |
| Material - Plating Termination | Tin                    |
| Material - Resin               | Liquid Crystal Polymer |
| Net Weight                     | 0.630/g                |
| Number of Rows                 | 1                      |
| Orientation                    | Right Angle            |
| Packaging Type                 | Tray                   |
| PCB Locator                    | Yes                    |
| PCB Retention                  | Yes                    |
| PCB Thickness - Recommended    | 1.60mm, 2.40mm         |
| PC Tail Length                 | 3.20mm                 |
| Pitch - Mating Interface       | 2.50mm                 |
| Pitch - Termination Interface  | 2.50mm                 |
| Plating min - Mating           | 1.524µm                |
| Plating min - Termination      | 1.524µm                |

|                               |                |
|-------------------------------|----------------|
| Polarized to Mating Part      | Yes            |
| Polarized to PCB              | Yes            |
| Shrouded                      | Yes            |
| Stackable                     | No             |
| Temperature Range - Operating | -40° to +125°C |
| Termination Interface Style   | Through Hole   |

---

## Mates With / Use With

### Mates with Part(s)

| Description                                                                                                                     | Part Number       |
|---------------------------------------------------------------------------------------------------------------------------------|-------------------|
| Nano-Fit Receptacle Housing, TPA Capable, 2.50mm Pitch, Single Row, 5 Circuits, Black, Glow-Wire Capable                        | <u>1053071205</u> |
| Nano-Fit Receptacle Housing, TPA Capable, 2.50mm Pitch, Single Row, 5 Circuits, Black, Glow-Wire Capable, for UL 1569/1007 Wire | <u>2263541205</u> |
| Nano-Fit-to-Nano-Fit Single Row Off-the-Shelf (OTS) Cable Assemblies                                                            | <u>145130</u>     |