



**Part Number :** [1054052304](#)

**Product Description :** Nano-Fit Right-Angle Header, Surface Mount, 2.50mm Pitch, Dual Row, 4 Circuits, 0.76µm Gold (Au) Plating, Natural, Glow-Wire Capable

**Series Number :** 105405

**Status :** Active

**Product Category :** PCB Headers and Receptacles



---

## Documents & Resources

### Drawings

[1054052304\\_sd.pdf](#)

[PK-105405-001-000.pdf](#)

### 3D Models and Design Files

[STEP AP242](#)

[SOLIDWORKS](#)

[Creo](#)

[Symbol and Footprint \(Multi-Format\)](#)

[SYM-105405-XX04-001.zip](#)

### Specifications

[AS-105405-001-001.pdf](#)

[1054051000-PS-CH-000.pdf](#)

[1054051000-PS-ES-000.pdf](#)

[1054051000-PS-SK-000.pdf](#)

[PS-105405-001-001.pdf](#)

[1054050000-TS-000.pdf](#)

---

## Product Environment Compliance

### Compliance

|            |                                                                                                              |
|------------|--------------------------------------------------------------------------------------------------------------|
| GADSL/IMDS | Compliant with Exemption 44; 34; 33                                                                          |
| China RoHS | <br>per SJ/T 11365-2006 |

|                    |                                                    |
|--------------------|----------------------------------------------------|
| EU ELV             | Not Relevant                                       |
| Low-Halogen Status | Low-Halogen per IEC 61249-2-21                     |
| REACH SVHC         | Not Contained per D(2025)4165-DC<br>(25 June 2025) |
| EU RoHS            | Compliant per EU 2015/863                          |

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

---

**Part Details**

**General**

|                |                                                                                                                                      |
|----------------|--------------------------------------------------------------------------------------------------------------------------------------|
| Status         | Active                                                                                                                               |
| Category       | PCB Headers and Receptacles                                                                                                          |
| Series         | 105405                                                                                                                               |
| Description    | Nano-Fit Right-Angle Header, Surface Mount, 2.50mm Pitch, Dual Row, 4 Circuits, 0.76µm Gold (Au) Plating, Natural, Glow-Wire Capable |
| Application    | Power, Wire-to-Board                                                                                                                 |
| Component Type | PCB Header                                                                                                                           |
| Product Name   | Nano-Fit                                                                                                                             |
| UPC            | 889056260060                                                                                                                         |

**Agency**

|    |        |
|----|--------|
| UL | E29179 |
|----|--------|

## Electrical

|                               |                  |
|-------------------------------|------------------|
| Current - Maximum per Contact | 7.0A             |
| Voltage - Maximum             | 250V AC (RMS)/DC |

## Physical

|                                |                        |
|--------------------------------|------------------------|
| Breakaway                      | No                     |
| Circuits (Loaded)              | 4                      |
| Circuits (maximum)             | 4                      |
| Color - Resin                  | Natural                |
| Durability (mating cycles max) | 50                     |
| First Mate / Last Break        | No                     |
| Glow-Wire Capable              | Yes                    |
| Keying to Mating Part          | Yes                    |
| Lock to Mating Part            | Yes                    |
| Material - Metal               | Brass                  |
| Material - Plating Mating      | Gold                   |
| Material - Plating Termination | Tin                    |
| Material - Resin               | Liquid Crystal Polymer |
| Net Weight                     | 0.800/g                |
| Number of Rows                 | 2                      |
| Orientation                    | Right Angle            |
| Packaging Type                 | Embossed Tape on Reel  |
| PCB Locator                    | No                     |
| PCB Retention                  | Yes                    |
| PCB Thickness - Recommended    | 1.60mm                 |
| Pitch - Mating Interface       | 2.50mm                 |
| Pitch - Termination Interface  | 2.50mm                 |
| Plating min - Mating           | 0.762µm                |
| Plating min - Termination      | 0.762µm                |
| Polarized to Mating Part       | Yes                    |
| Polarized to PCB               | Yes                    |
| Shrouded                       | Yes                    |
| Temperature Range - Operating  | -40° to +125°C         |
| Termination Interface Style    | Surface Mount          |

---

# Mates With / Use With

## Mates with Part(s)

| Description                                                                                                                     | Part Number       |
|---------------------------------------------------------------------------------------------------------------------------------|-------------------|
| Nano-Fit Receptacle Housing, TPA Capable, 2.50mm Pitch, Dual Row, 4 Circuits, Natural, Glow-Wire Capable                        | <u>1053082204</u> |
| Nano-Fit Receptacle Housing, TPA Capable, 2.50mm Pitch, Dual Row, 4 Circuits, Natural, Glow-Wire Capable, for UL 1569/1007 Wire | <u>2263622204</u> |