



Part Number : [10883042](#)


Product Description : 2.54mm Pitch C-Grid
Breakaway Header, High Profile, Dual Row, Right
Angle, 4 Circuits, 8.13mm Mating Pin Length, Tin (Sn)
Plating

Series Number : 70216

Status : Active

Product Category : PCB Headers and Receptacles

Engineering Part Number : 70216-0118



Documents and Resources

Drawings

[010883042_sd.pdf](#)

[PK-70873-0353-001.pdf](#)

[STEP AP242](#)

[SOLIDWORKS](#)

[Creo](#)

[Symbol and Footprint \(Multi-Format\)](#)

Specifications

[713080001-AS-000.pdf](#)

[PS-70216-001.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	 per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)6375- DC (05 Nov 2025)
EU RoHS	Compliant per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	PCB Headers and Receptacles
Series	70216
Description	2.54mm Pitch C-Grid Breakaway Header, High Profile, Dual Row, Right Angle, 4 Circuits, 8.13mm Mating Pin Length, Tin (Sn) Plating
Application	Board-to-Board, Signal, Wire-to-Board
Component Type	PCB Header
Product Name	C-Grid
UPC	800755011715

Agency

CSA	LR19980
UL	E29179

Electrical

Current - Maximum per Contact	3.0A
Voltage - Maximum	250V

Physical

Breakaway	Yes
Circuits (Loaded)	4
Circuits (maximum)	4
Color - Resin	Black
Durability (mating cycles max)	25
First Mate / Last Break	No
Glow-Wire Capable	No
Lock to Mating Part	None
Material - Metal	Brass, Phosphor Bronze
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Material - Resin	Polyester
Net Weight	0.359/g
Number of Rows	2
Orientation	Right Angle
Packaging Type	Tube
PCB Locator	No
PCB Retention	None
PC Tail Length	2.79mm
Pitch - Mating Interface	2.54mm
Plating min - Mating	3.810µm
Plating min - Termination	3.810µm
Polarized to Mating Part	No
Polarized to PCB	No
Shrouded	No
Stackable	Yes
Temperature Range - Operating	-40° to +105°C
Termination Interface Style	Through Hole

Solder Process Data

Max-Duration	5
Lead-Free Process Capability	WAVE
Max-Cycle	1
Max-Temp	235

Mates With / Use With

Mates with Part(s)

Description	Part Number
C-Grid Right-Angle, Dual Row, Surface Mount PCB Receptacles	<u>71979</u>
C-Grid Vertical, Dual Row, High Profile, Surface Mount PCB Connectors	<u>71395</u>
C-Grid Vertical, Dual Row, High Profile, Through Hole PCB Receptacles	<u>71850</u>
2.54mm Pitch C-Grid Shunt Terminal Housings	<u>7859</u>