



Part Number : [1713209032](#)

Product Description : Impel 90 Ohm, 4 Pair Right-Angle Daughtercard, 1.90mm Pitch, Right Guided, 2 Columns, 16 Circuits, Plated Through Hole Dimension 0.36mm

Series Number : 171320

Status : Active

Product Category : Backplane Connectors



Documents and Resources

Drawings

[1713209032 sd.pdf](#)

[PK-78888-085-001.pdf](#)

3D Models and Design Files

[STEP AP242](#)

[SOLIDWORKS](#)

[Creo](#)

[1713201218-000.pdf](#)

[1713202061REVA-000.pdf](#)

[1713201218-000.zip](#)

[1713202061-000.zip](#)

Specifications

[1713209994-AS-000.pdf](#)

[AS-171320-990-001.pdf](#)

[AS-171320-991-001.pdf](#)

[AS-171320-992-001.pdf](#)

[PS-171320-999-001.pdf](#)

[PS-45499-002-001.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
------------	--------------

China RoHS	 per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)4165-DC (25 June 2025)
EU RoHS	Compliant per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Backplane Connectors
Series	171320
Description	Impel 90 Ohm, 4 Pair Right-Angle Daughtercard, 1.90mm Pitch, Right Guided, 2 Columns, 16 Circuits, Plated Through Hole Dimension 0.36mm
Application	Coplanar, Daughtercard
Component Type	PCB Receptacle
Product Name	Impel
UPC	191128235341

Agency

UL	E29179
----	--------

Electrical

Current - Maximum per Contact	0.75A
Data Rate	40.0 Gbps
Impedance	90Ω
Shield Type	Full Shield
Voltage - Maximum	29.9V AC (RMS)/DC

Physical

Circuits (Loaded)	16
Circuits (maximum)	16
Color - Resin	Black
Durability (mating cycles max)	200
First Mate / Last Break	No
Guide to Mating Part	Yes
Keying to Mating Part	None
Material - Metal	High Performance Alloy (HPA)
Material - Plating Mating	Gold
Material - Plating Termination	Tin
Material - Resin	High Temperature Thermoplastic
Net Weight	13.182/g
Number of Columns	2
Number of Pairs	4
Number of Rows	8
Orientation	Right Angle
Packaging Type	Tray
PCB Locator	Yes
PCB Retention	Yes
PCB Thickness - Recommended	1.00mm
PC Tail Length	1.30mm
Pitch - Mating Interface	1.90mm
Pitch - Termination Interface	1.90mm
Plating min - Mating	0.762μm
Temperature Range - Operating	-55° to +85°C

Solder Process Data

Lead-Free Process Capability	N/A
------------------------------	-----

Mates With / Use With

Mates with Part(s)

Description	Part Number
Mates With	Impel Cable