



Part Number : [1720430205](#)
Product Description : Super Sabre Right-Angle Header, 2 Circuit, Long Solder Tail without Board Lock, Complies with UL1977 Finger Proof Standards, Glow-Wire Capable
Series Number : 172043
Status : Active
Product Category : PCB Headers and Receptacles



Documents and Resources

Drawings

[1720430205 sd.pdf](#)
[PK-43789-001-001.pdf](#)

3D Models and Design Files

[STEP AP242](#)
[SOLIDWORKS](#)
[Creo](#)
[Symbol and Footprint \(Multi-Format\)](#)
[SYM-172043-0201-001.zip](#)

Specifications

[PS-171825-001-001.pdf](#)
[TS-171825-001-001.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	 per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Compliant per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	PCB Headers and Receptacles
Series	172043
Description	Super Sabre Right-Angle Header, 2 Circuit, Long Solder Tail without Board Lock, Complies with UL1977 Finger Proof Standards, Glow-Wire Capable
Application	Power, Signal, Wire-to-Board
Comments	Operating Temperature Per USCAR-2; Class 3
Component Type	PCB Header
Product Name	Super Sabre
UPC	887191565668

Agency

CSA	LR19980
UL	E29179

Electrical

Current - Maximum per Contact	30.0A per blade
-------------------------------	-----------------

Voltage - Maximum	600V AC (RMS)
-------------------	---------------

Physical

Breakaway	No
Circuits (Loaded)	2
Circuits (maximum)	2
Color - Resin	Black
Durability (mating cycles max)	25
First Mate / Last Break	No
Glow-Wire Capable	Yes
Lock to Mating Part	Yes
Material - Metal	Copper
Material - Plating Mating	Silver
Material - Plating Termination	Matte Tin
Material - Resin	High Temperature Thermoplastic
Net Weight	3.261/g
Number of Rows	1
Orientation	Right Angle
Packaging Type	Tray
PCB Retention	None
PC Tail Length	5.33mm
Pitch - Mating Interface	7.50mm
Plating min - Mating	2.540µm
Plating min - Termination	2.540µm
Polarized to Mating Part	Yes
Temperature Range - Operating	-40° to +125°C
Termination Interface Style	Through Hole

Solder Process Data

Max-Duration	30
Lead-Free Process Capability	SMC&WAVE
Max-Cycle	3
Max-Temp	260

Mates With / Use With

Mates with Part(s)

Description	Part Number
Super Sabre Single Row Receptacle Housings	<u>172672</u>