

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [1721405808](#)  
**Status:** **Active**  
**Overview:** [Impel and Impel Plus Backplane Solutions](#)  
**Description:** Impel 90 Ohm, 4 Pair Right-Angle Header, 1.90mm Pitch, Left Guided, 8 Columns, 64 Circuits, Pin Length 5.50, Plated Through Hole Dimension 0.36mm

**Documents:**

<a href="#">3D Model</a>	<a href="#">Symbol Footprint Data SYM-172140-5107 (PDF)</a>
<a href="#">Drawing (PDF)</a>	<a href="#">Symbol Footprint Data SYM-172140-5108 (PDF)</a>
<a href="#">3D Model (PDF)</a>	<a href="#">Symbol Footprint Data SYM-172140-5207 (PDF)</a>
<a href="#">Product Specification PS-171320-999-001 (PDF)</a>	<a href="#">Symbol Footprint Data SYM-172140-5208 (PDF)</a>
<a href="#">Application Specification AS-171320-990-001 (PDF)</a>	<a href="#">Symbol Footprint Data SYM-172140-5807 (PDF)</a>
<a href="#">Application Specification AS-171320-991-001 (PDF)</a>	<a href="#">Symbol Footprint Data SYM-172140-5808 (PDF)</a>
<a href="#">Application Specification AS-171320-992-001 (PDF)</a>	<a href="#">RoHS Certificate of Compliance (PDF)</a>
<a href="#">Packaging Specification PK-78888-314-001 (PDF)</a>	

**General**

Product Family	Backplane Connectors
Series	<a href="#">172140</a>
Application	Backplane, Coplanar
Application Tooling Documents	TM-622018899
Component Type	PCB Header
Overview	<a href="#">Impel and Impel Plus Backplane Solutions</a>
Product Name	Impel
UPC	889056026413

**Physical**

Circuits (Loaded)	64
Circuits (maximum)	64
Color - Resin	Black
Durability (mating cycles max)	200
First Mate / Last Break	No
Guide to Mating Part	Yes
Keying to Mating Part	None
Material - Metal	High Performance Alloy (HPA)
Material - Plating Mating	Gold
Material - Plating Termination	Tin
Material - Resin	High Temperature Thermoplastic
Net Weight	28.265/g
Number of Columns	8
Number of Pairs	4
Number of Rows	8
Orientation	Right Angle
PC Tail Length	1.30mm
PCB Locator	No
PCB Retention	None
PCB Thickness - Recommended	1.00mm
Packaging Type	Tray
Pitch - Mating Interface	1.90mm
Pitch - Termination Interface	1.90mm
Plating min - Mating	0.762µm
Temperature Range - Operating	-55° to +85°C

**Electrical**

Current - Maximum per Contact	0.75A
Data Rate	40.0 Gbps
Impedance	90Ω



Series image - Reference only

**EU ELV**

**Not Relevant**

**EU RoHS**

**Compliant**

**REACH SVHC**

Not Contained Per -  
D(2020)4578-DC (25  
June 2020)

**Halogen-Free**

**Status**

**Low-Halogen**

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

**China RoHS**

Green Image

Not Relevant

Not Contained

**Search Parts in this Series**

[172140 Series](#)

**Mates With**

Impel Right-Angle Daughtercard  
[1713205038](#)

**Application Tooling | FAQ**

*Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.*

**Global**

**Description**

**Product #**

Impel Daughtercard	<a href="#">622018959</a>
Module Installation	
Press-In Tool	

Shield Type	Full Shield
Voltage - Maximum	150V AC (RMS)/DC
<b>Solder Process Data</b>	
Lead-free Process Capability	N/A
<b>Material Info</b>	
<b>Reference - Drawing Numbers</b>	
Application Specification	AS-171320-990-001, AS-171320-991-001, AS-171320-992-001
Packaging Specification	PK-78888-314-001
Product Specification	PS-171320-999-001
Sales Drawing	SD-172140-0004-001
Symbol/Footprint Data	SYM-172140-5107, SYM-172140-5108, SYM-172140-5207, SYM-172140-5208, SYM-172140-5807, SYM-172140-5808

This document was generated on 08/14/2020

**PLEASE CHECK [WWW.MOLEX.COM](http://WWW.MOLEX.COM) FOR LATEST PART INFORMATION**