





COMMENT:
ALL RIGHTS ARE RESERVED BY US FOR THIS DRAWING. WITHOUT OUR PRIOR CONSENT,
IT MAY NEITHER BE DUBICATED NOR MADE AVAILABLE TO A THIRD PARTY.
AND IT ALSO MAY NOT BE IMPROPERLY USED BY TE RECEIVER, OR A THIRD PARTY.



FUxx*)S7-0970
e.g. FU15S7-0970

*) xx No. of contacts 09, 15, 25 or 37

MATERIAL NUMBER	xx *)	A [mm]	B [mm]	C [mm]
1731092064	09	30.8	16.4	25
1731092184	15	39.1	24.7	33.3
1731092502	25	53	38.5	47.04
1731090616	37	69.3	54.9	63.5

Crimp contacts not supplied with connector. Contacts must be ordered separately.

3	1	Shell	Steel	tin plated
2	1	Insulator rear part	PEI (-55°C to +130°C)	green
1	1	Insulator front part	PBT acc. UL94V-0	green
No.	St.	Part	Type Description/Material	Surface plating/Colour/Class

FUNCTIONAL SYMBOLS ▽ = 0 ▽ = 0 ▽ = 0	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION									
	DIMENSION UNITS mm		SCALE 2:1		MEASUREMENTS WITHOUT TOLERANCE ACC. TO ISO 2768-mK			molex FCT D-Sub Crimp Connector		
					CURRENT REVISION					
					DRWN: DRAWN BY mteubel 12-08-2025 APPR: APPR BY mbisl 12-08-2025					
	3 24140				INITIAL REVISION			PRODUCT CUSTOMER DRAWING		
	2 24410									
	1				MATERIAL NUMBER see table			REVISION 3		
	REV. CH.-NO.									
	REPLACEMENT FOR: 1731092064_Rev. A		FRIST ANGLE PROJECTION 		DRAWING A3-SIZE		DOCUMENT NUMBER FUxxS7-0970		CUSTOMER GENERAL MARKET	