



Part Number : [1731140526](#)
Product Description : FCT Standard-Density D-Sub Crimp Housing, Male, Tin Plated Shell with Dimples, Non-Magnetic, 25 Circuits, Green Front and Rear Insulator
Series Number : 173114
Status : Obsolete
Product Category : D-Sub Connectors
Engineering Part Number : FU25P7-2710




Illustration only.
The pole size may deviate from the image.

Documents and Resources

Drawings

[1731140526_sd.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	 per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Reviewed per IEC 61249-2-21
REACH SVHC	Not Reviewed per D(2025)6375-DC (05 Nov 2025)
EU RoHS	Compliant per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Obsolete
Category	D-Sub Connectors
Series	173114
Description	FCT Standard-Density D-Sub Crimp Housing, Male, Tin Plated Shell with Dimples, Non-Magnetic, 25 Circuits, Green Front and Rear Insulator
IP Rating	IP20
Magnetic	No
Product Name	FCT Products
Type	Standard Density
UPC	191130629770

Electrical

Shielded	Yes
----------	-----

Physical

Circuits (Loaded)	0
Circuits (maximum)	25
Color - Resin	Green
Gender	Male
Material - Resin	PBT
Material - Shell	Brass
Net Weight	18.000/g
Number of Rows	2
Orientation	Straight
Packaging Type	Carton
Panel Mount	Front or Rear

Panel Mount Method	Flange
PCB Locator	No
PCB Retention	None
Pitch - Mating Interface	2.84mm
Pitch - Termination Interface	2.84mm
Plating - Shell	Tin
Polarized to Mating Part	Yes
Polarized to PCB	No
Ports	1
Temperature Range - Operating	-55° to +115°C
Termination Style	Crimp
Waterproof / Dustproof	No
Waterproof / Dustproof Type	IP20

Mates With / Use With

Mates with Part(s)

Description	Part Number
Mates With	FCT Standard-Density D-Sub, Size 3, 25 Position, Socket

This document was generated on Feb 27, 2026