



Part Number : [192110002](#)
Product Description : Krimptite Wire Pin Terminal
for 12-10 AWG Wire, Mylar Tape Carrier
Series Number : 19211
Status : Active
Product Category : Crimp Terminals
Engineering Number : WP-1210T
Packaging Alternative : [192110001](#) (Bag)



Documents & Resources

- Drawings**
[192110002_sd.pdf](#)
- Specifications**
[PS-19902-015-001.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	 per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)4165-DC (25 June 2025)
EU RoHS	Compliant per EU 2015/863

- Compliance Statements
- EU RoHS
 - REACH SVHC
 - Low-Halogen

- Industry Documents
- IPC 1752A Class C
 - IPC 1752A Class D
 - Molex Product Compliance Declaration
 - IEC-62474

- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Crimp Terminals
Series	19211
Description	Krimptite Wire Pin Terminal for 12-10 AWG Wire, Mylar Tape Carrier
Application	Power, Wire-to-Component
Comments	Pin Length 11.43mm
Product Name	Wire Pin,Krimptite
UPC	800753053205

Agency

CSA	LR18689
UL	E32244

Physical

Gender	Male
Material - Metal	Copper
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Net Weight	1.465/g
Packaging Type	Adhesive Tape on Reel
Plating min - Mating	0.762µm
Plating min - Termination	0.762µm
Termination Interface Style	Crimp or Compression
Wire Insulation Diameter	3.45mm max.
Wire Size (AWG)	10, 12

Wire Size mm ²	N/A
---------------------------	-----

Application Tooling

Global

Description	Part Number
ATP Crimp Dies for the Tape Crimp Module and ATP-101 & 301 Press	<u>190270088</u>
Mini-Mac Applicator	<u>638851000</u>