




Part Number : [1703351408](#)
Product Description : Impact 85 Ohm Plus 4 Pair
Vertical Header, Unguided, Open End Wall, 14
Columns, 168 Circuits, Pin Length 5.50mm, Plated
Through Hole Dimension 0.39mm, Lead-Free
Series Number : 170335
Status : Active
Product Category : Backplane Connectors



Documents and Resources

Drawings

- [1703351408 sd.pdf](#)
- [PK-70873-7701-001.pdf](#)
- [SYM-170335-1408-001.zip](#)

Specifications

- [AS-76060-990-001.pdf](#)
- [PS-170540-999-001.pdf](#)
- [PS-45499-002-001.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Compliant with Exemption 44; 34; 33
China RoHS	 per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Compliant per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC

- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Backplane Connectors
Series	170335
Description	Impact 85 Ohm Plus 4 Pair Vertical Header, Unguided, Open End Wall, 14 Columns, 168 Circuits, Pin Length 5.50mm, Plated Through Hole Dimension 0.39mm, Lead-Free
Application	Conventional, Mezzanine
Component Type	PCB Header
Product Name	Impact
UPC	887191299396

Agency

UL	E29179
----	--------

Electrical

Current - Maximum per Contact	0.75A
Data Rate	25.0 Gbps
Impedance	85Ω
Shielded	No
Shield Type	N/A

Voltage - Maximum	30V AC (RMS)/DC
-------------------	-----------------

Physical

Circuits (Loaded)	168
Circuits (maximum)	168
Color - Resin	Gray
Durability (mating cycles max)	200
First Mate / Last Break	No
Guide to Mating Part	No
Keying to Mating Part	None
Material - Metal	High Performance Alloy (HPA)
Material - Plating Mating	Gold
Material - Plating Termination	Tin
Material - Resin	High Temperature Thermoplastic
Net Weight	4.711/g
Number of Columns	14
Number of Pairs	4
Number of Rows	12
Orientation	Vertical
Packaging Type	Tray
PCB Locator	No
PCB Retention	None
PCB Thickness - Recommended	1.00mm
PC Tail Length	1.40mm
Pitch - Mating Interface	1.35mm, 1.90mm
Pitch - Termination Interface	1.35mm, 1.90mm
Plating min - Mating	0.762µm
Polarized to PCB	No
Stackable	No
Temperature Range - Operating	-55° to +85°C
Termination Interface Style	Through Hole - Compliant Pin

Solder Process Data

Lead-Free Process Capability	N/A
------------------------------	-----

Mates With / Use With

Mates with Part(s)

Description	Part Number
Impact 85 Ohm Plus 4 Pair Right-Angle Daughtercards	<u>170340</u>
Impact 85 Ohm Plus 4 Pair Mezzanine Receptacles	<u>170390</u>

Application Tooling

This document was generated on Feb 27, 2026