



Part Number : [2076025008](#)
Product Description : Grounding Jumper without
Insulation, Flat-to-Flat, 48x24/36 Braid Type,
607.00mm Length
Series Number : 207602
Status : Active
Product Category : Busbars



Documents & Resources

Drawings

[2076025008_sd.pdf](#)

3D Models and Design Files

[STEP AP242](#)

[SOLIDWORKS](#)

[Creo](#)

Specifications

[2076025000-PS-000.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	 per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)4165-DC (25 June 2025)
EU RoHS	Compliant per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Busbars
Series	207602
Description	Grounding Jumper without Insulation, Flat-to-Flat, 48x24/36 Braid Type, 607.00mm Length
Keyword	grounding jumpers, grounding strap, grounding straps, ground strap, ground straps, busbar
Product Name	Grounding Jumper
UPC	191128899017

Electrical

Current - Maximum per Contact	105.0A
-------------------------------	--------

Physical

Approximate AWG Equivalent	6
Approximate Circular Mils	28800
Braid Type	48x24/36
Insulation	None
Length	607.00mm
Material - Metal	Copper
Material - Plating Mating	Tin
Material - Plating Termination	Tin

Orientation	Flat-to-Flat
Packaging Type	Carton