



Part Number : [1704805026](#)

Product Description : Impact 85 Ohm Plus 5 Pair Right-Angle Daughtercard, Right Guided, 16 Columns, 240 Circuits, Plated Through Hole Dimension 0.39mm, Lead Free

Series Number : 170480

Status : Active

Product Category : Backplane Connectors



Documents and Resources

Drawings

[1704805026 sd.pdf](#)

[PK-70873-611-001.pdf](#)

3D Models and Design Files

[STEP AP242](#)

[SOLIDWORKS](#)

[Creo](#)

[SYM-170480-5026-001.zip](#)

[EE-170480-0001-001.pdf](#)

[SP-170480-0003-001.zip](#)

Specifications

[AS-76060-990-001.pdf](#)

[PS-170540-999-001.pdf](#)

[PS-45499-002-001.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	 per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21

REACH SVHC	Not Contained per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Compliant per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Backplane Connectors
Series	170480
Description	Impact 85 Ohm Plus 5 Pair Right-Angle Daughtercard, Right Guided, 16 Columns, 240 Circuits, Plated Through Hole Dimension 0.39mm, Lead Free
Application	Conventional, Daughtercard
Component Type	PCB Receptacle
Product Name	Impact
UPC	887191152950

Agency

UL	E29179
----	--------

Electrical

Current - Maximum per Contact	0.75A
Data Rate	25.0 Gbps
Impedance	85Ω
Shielded	No
Shield Type	N/A
Voltage - Maximum	30V AC (RMS)/DC

Physical

Circuits (Loaded)	240
Circuits (maximum)	240
Color - Resin	Gray
Durability (mating cycles max)	200
First Mate / Last Break	No
Flammability	94V-0
Guide to Mating Part	Yes
Keying to Mating Part	None
Material - Metal	High Performance Alloy (HPA)
Material - Plating Mating	Gold
Material - Plating Termination	Tin
Material - Resin	High Temperature Thermoplastic
Net Weight	35.034/g
Number of Columns	16
Number of Pairs	5
Number of Rows	15
Orientation	Right Angle
Packaging Type	Tray
PCB Locator	No
PCB Retention	None
PCB Thickness - Recommended	1.00mm
PC Tail Length	1.20mm
Pitch - Mating Interface	1.35mm, 1.90mm
Pitch - Termination Interface	1.35mm, 1.90mm
Plating min - Mating	0.762μm
Polarized to PCB	No
Stackable	No

Temperature Range - Operating	-55° to +85°C
Termination Interface Style	Through Hole - Compliant Pin

Solder Process Data

Lead-Free Process Capability	N/A
------------------------------	-----

Mates With / Use With

Mates with Part(s)

Description	Part Number
Impact 85 Ohm Plus 5 Pair Vertical Backplane Headers	<u>170475</u>

Application Tooling