



Part Number : [1708140033](#)
Product Description : NeoScale High-Speed
Mezzanine Receptacle, 2.80mm Pitch, 6x20, 120
Triads-85 Ohm (360 Circuits), 18.00mm Connector
Height
Series Number : 170814
Status : Active
Product Category : Board-to-Board Connectors



Documents and Resources

Drawings

[1708140033 sd.pdf](#)
[PK-170814-002-001.pdf](#)

3D Models and Design Files

[STEP AP242](#)
[SOLIDWORKS](#)
[Creo](#)
[EE-170807-0004-001.pdf](#)
[SP-170807-0004-001.zip](#)

Specifications

[PS-170807-0001-001.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	 per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)4165-DC (25 June 2025)
EU RoHS	Compliant per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Board-to-Board Connectors
Series	170814
Description	NeoScale High-Speed Mezzanine Receptacle, 2.80mm Pitch, 6x20, 120 Triads-85 Ohm (360 Circuits), 18.00mm Connector Height
Application	Board-to-Board, Signal, Mezzanine
Component Type	PCB Receptacle, Receptacle
Product Name	NeoScale
UPC	889056130011

Agency

UL	E29179
----	--------

Electrical

Current - Maximum per Contact	1.0A
Grounding to PCB	No
Voltage - Maximum	30V AC (RMS)

Physical

Circuits (Loaded)	360
Circuits (maximum)	360
Color - Resin	Black
Durability (mating cycles max)	100
Flammability	94V-0
Glow-Wire Capable	No
Guide to Mating Part	Yes
Keying to Mating Part	None
Lock to Mating Part	None
Material - Metal	High Performance Alloy (HPA)
Material - Plating Mating	Gold
Material - Plating Termination	Tin
Material - Resin	Liquid Crystal Polymer
Net Weight	33.992/g
Number of Rows	6
Orientation	Vertical
Packaging Type	Tray
PCB Locator	Yes
PCB Retention	Yes
Pitch - Mating Interface	2.80mm
Pitch - Termination Interface	2.80mm
Plating min - Mating	0.762µm
Plating min - Termination	2.540µm
Polarized to Mating Part	Yes
Polarized to PCB	Yes
Temperature Range - Operating	-55° to +85°C
Termination Interface Style	Solder or Weld

Solder Process Data

Max-Duration	20
Lead-Free Process Capability	REFLOW
Max-Cycle	1
Max-Temp	260

This document was generated on Feb 27, 2026