



**Part Number :** [1715741834](#)

**Product Description :** Impact 100 Ohm 4-Pair Right-Angle Orthogonal Direct Header, Unguided, with Outtrigger, 8 Column, 32 Differential Pair, 270° Mate Position, Pin Length 4.90mm, Plated Through-Hole Dimension 0.46mm, Lead Free

**Series Number :** 171574

**Status :** Active

**Product Category :** Backplane Connectors



---

## Documents & Resources

### Drawings

[1715741834 sd.pdf](#)

[PK-70873-8020-001.pdf](#)

### 3D Models and Design Files

[STEP AP242](#)

[SOLIDWORKS](#)

[Creo](#)

### Specifications

[AS-76060-9999-001.pdf](#)

[AS-76850-990-001.pdf](#)

[PS-45499-002-001.pdf](#)

[PS-76060-999-001.pdf](#)

---

## Product Environment Compliance

### Compliance

GADSL/IMDS	Not Relevant
China RoHS	per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)4165-DC

	(25 June 2025)
EU RoHS	Compliant per EU 2015/863

### Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

### Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

### Substances of Interest

- PFAS

### EU RoHS Certificate of Compliance

### Additional Product Compliance Information

## Part Details

### General

Status	Active
Category	Backplane Connectors
Series	171574
Description	Impact 100 Ohm 4-Pair Right-Angle Orthogonal Direct Header, Unguided, with Outrigger, 8 Column, 32 Differential Pair, 270° Mate Position, Pin Length 4.90mm, Plated Through-Hole Dimension 0.46mm, Lead Free
Application	Orthogonal Direct
Component Type	PCB Header
Product Name	Impact
UPC	887191727165

### Agency

UL	E29179
----	--------

## Electrical

Current - Maximum per Contact	0.75A
Data Rate	25.0 Gbps
Impedance	100Ω
Shielded	No
Shield Type	N/A
Voltage - Maximum	30V AC (RMS)/DC

## Physical

Circuits (Loaded)	96
Circuits (maximum)	96
Color - Resin	Black
Durability (mating cycles max)	200
First Mate / Last Break	No
Flammability	94V-0
Guide to Mating Part	No
Keying to Mating Part	None
Material - Metal	High Performance Alloy (HPA)
Material - Plating Mating	Gold
Material - Plating Termination	Tin
Material - Resin	High Temperature Thermoplastic
Net Weight	19.776/g
Number of Columns	8
Number of Pairs	4
Number of Rows	12
Orientation	Vertical
Packaging Type	Tray
PCB Locator	No
PCB Retention	None
PCB Thickness - Recommended	1.00mm
PC Tail Length	1.40mm
Pitch - Mating Interface	1.90mm
Pitch - Termination Interface	1.90mm
Plating min - Mating	0.762μm
Polarized to PCB	No

Stackable	No
Temperature Range - Operating	-55° to +85°C
Termination Interface Style	Through Hole - Compliant Pin

### Solder Process Data

Lead-Free Process Capability	N/A
------------------------------	-----

---

### Mates With / Use With

#### Mates with Part(s)

Description	Part Number
Impact 100 Ohm 4 Pair Right-Angle Orthogonal Daughtercards	<u>76850</u>

---

This document was generated on Oct 02, 2025