



Part Number : [2174911112](#)
Product Description : Pre-Crimped Lead iGrid-Female-to-Pigtail, Tin (Sn) Plating, 150.00mm Length, 24 AWG, Black
Series Number : 217491
Status : Active
Product Category : Power and Signal Cable Assemblies



Documents & Resources

- Drawings
- [2174911112 sd.pdf](#)
 - [STEP AP242](#)
 - [SOLIDWORKS](#)
 - [Creo](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	 per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2024)6225-DC (07 Nov 2024)
EU RoHS	Compliant per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C

- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Power and Signal Cable Assemblies
Series	217491
Description	Pre-Crimped Lead iGrid-Female-to-Pigtail, Tin (Sn) Plating, 150.00mm Length, 24 AWG, Black
Application	Signal, Wire-to-Board
Assembly Configuration	Pre-crimped Lead Only
Connector to Connector	iGrid Crimp Terminals
Product Name	iGrid
UPC	195842118867

Electrical

Voltage - Maximum	250V AC (RMS)/DC
-------------------	------------------

Physical

Cable Length	150.00mm
Circuits (Loaded)	1
Circuits (maximum)	1
Color - Resin	Black
Gender	Female-Pigtail
Material - Metal	Copper Alloy
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Material - Resin	PVC

Net Weight	0.442/g
Number of Rows	1
Packaging Type	Bag
Single Ended	Yes
Termination Interface Style	Crimp or Compression
Wire/Cable Type	UL 10002
Wire Size (AWG)	24