



Part Number : [2183730001](#)
Product Description : SW1 11.00mm Screw Mount
Locking Pin in Bag, 20.00mm Engagement Length
Series Number : 218373
Status : Active
Product Category : PCB Headers and Receptacles



Documents & Resources

Drawings

[2183730001_sd.pdf](#)

3D Models and Design Files

[STEP AP242](#)

[SOLIDWORKS](#)

[Creo](#)

Specifications

[2182310001-AS-000.pdf](#)

[2182310001-PS-000.pdf](#)

[2182310001-TS-000.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not saleable
China RoHS	 per SJ/T 11365-2006
EU ELV	Not saleable
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2024)7663-DC (21 Jan 2025)
EU RoHS	Compliant per EU 2015/863

[Compliance Statements](#)

- EU RoHS
- REACH SVHC

- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	PCB Headers and Receptacles
Series	218373
Description	SW1 11.00mm Screw Mount Locking Pin in Bag, 20.00mm Engagement Length
Application	Power, Wire-to-Board, Wire-to- Busbar
Component Type	PCB Header
Product Name	SW1
UPC	195842373327

Electrical

Current - Maximum per Contact	300.0A
Voltage - Maximum	1000V

Physical

Breakaway	No
Circuits (Loaded)	1
Circuits (maximum)	1
Diameter	11.00mm
Durability (mating cycles max)	50
First Mate / Last Break	No

Glow-Wire Capable	No
Height Above Board	20.00mm
Material - Metal	Copper Alloy
Material - Plating Mating	Silver
Material - Plating Termination	Silver
Net Weight	18.610/g
Number of Rows	1
Orientation	Vertical
Packaging Type	Bag
PCB Thickness - Recommended	2.00mm min.
Pitch - Mating Interface	N/A
Polarized to Mating Part	No
Polarized to PCB	No
Temperature Range - Operating	-40° to +125°C
Termination Interface Style	Screw