



Part Number : [192740004](#)

Product Description : Quixon Quick Disconnect,
InsulKrimp Style, Female, Partially Insulated Blue,
16-14 AWG, Continuous Strip

Series Number : 19274

Status : Active

Product Category : Quick Disconnects

Engineering Part Number : BBZ-2141-LIF



Documents and Resources

Drawings

[192740004_sd.pdf](#)

Specifications

[PS-19902-012-001.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	 per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)6375-DC (05 Nov 2025)
EU RoHS	Compliant per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration

- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Quick Disconnects
Series	19274
Description	Quixon Quick Disconnect, InsulKrimp Style, Female, Partially Insulated Blue, 16-14 AWG, Continuous Strip
Comments	Low Insertion Force
Product Name	InsulKrimp,Quixon
Type	Quixon Low Insertion Disconnect
UPC	884982564985

Agency

CSA	LR18689
UL	E79133

Electrical

Voltage - Maximum	600V
-------------------	------

Physical

Barrel Type	Closed
Color - Resin	Blue
Flammability	94V-0
Gender	Female
Glow-Wire Capable	No
Insulated	Partial
Insulation	PVC

Lock to Mating Part	None
Material - Metal	Brass
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Net Weight	0.778/g
Orientation	Straight
Packaging Type	Reel
Plating min - Mating	2.540µm
Plating min - Termination	2.540µm
Tab Thickness	0.41mm
Tab Width	7.87mm
Temperature Range - Operating	-55° to +105°C
Wire Insulation Diameter	3.50mm
Wire Size (AWG)	14, 16

Application Tooling

Global

Description	Part Number
Mini-Mac Applicator Mechanical Feed-Metal Strip	<u>638814600</u>