



Part Number : [351500209](#)
Product Description : VersaBlade Hybrid Receptacle Housing, without Mounting Ears, 2 Circuits, Natural, Glow-Wire Capable
Series Number : 35150
Status : Active
Product Category : Connector Housings



Documents & Resources

Drawings

[351500209 sd.pdf](#)

3D Models and Design Files

[STEP AP242](#)

[SOLIDWORKS](#)

[Creo](#)

Specifications

[351500000AS ENG-000.pdf](#)

[351500000AS KOR-000.pdf](#)

[PK-35150-002-001.pdf](#)

[PS-35150-003-001.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	 per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)4165-DC (25 June 2025)
EU RoHS	Compliant per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Connector Housings
Series	35150
Description	VersaBlade Hybrid Receptacle Housing, without Mounting Ears, 2 Circuits, Natural, Glow-Wire Capable
Application	Power, Wire-to-Wire
Product Name	VersaBlade
UPC	756054256411

Agency

CSA	LR19980
UL	E29179

Physical

Breakaway	No
Circuits (maximum)	2
Color - Resin	Natural
Flammability	94V-0

Gender	Receptacle
Glow-Wire Capable	Yes
Keying to Mating Part	None
Lock to Mating Part	Yes
Material - Resin	PET/PC
Net Weight	1.706/g
Number of Rows	1
Packaging Type	Bag
Panel Mount	No
Pitch - Mating Interface	6.20mm
Pitch - Termination Interface	6.20mm
Polarized to Mating Part	Yes
Stackable	No
Temperature Range - Operating	-40° to +110°C

Mates With / Use With

Mates with Part(s)

Description	Part Number
VersaBlade Hybrid Plug Housings	<u>35151</u>

Use with Part(s)

Description	Part Number
VersaBlade Terminal Position Assurance (TPA) Retainer, 6.20mm Pitch, 2 Circuits, Natural	<u>351500290</u>
VersaBlade Terminal Position Assurance (TPA) Retainer, 6.20mm Pitch, 2 Circuits, Red	<u>351500292</u>
VersaBlade Terminal Position Assurance (TPA) Retainer, 6.20mm Pitch, 2 Circuits, Yellow	<u>351500293</u>
VersaBlade Terminal Position Assurance (TPA) Retainer, 6.20mm Pitch, 2 Circuits, Blue	<u>351500294</u>
VersaBlade Male Crimp Terminals	<u>35745</u>

