



Part Number : [2185091084](#)

Product Description : Milli-Grid-to-Milli-Grid Off-the-Shelf (OTS) Cable Assembly, 2.00mm Pitch, Dual Row, 600.00mm Length, 8 Circuits, Black

Series Number : 218509

Status : Active

Product Category : Power and Signal Cable Assemblies



Documents & Resources

Drawings

[2185091084 sd.pdf](#)

[STEP AP242](#)

[SOLIDWORKS](#)

[Creo](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	 per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2024)7663-DC (21 Jan 2025)
EU RoHS	Compliant per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C

- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Power and Signal Cable Assemblies
Series	218509
Description	Milli-Grid-to-Milli-Grid Off-the-Shelf (OTS) Cable Assembly, 2.00mm Pitch, Dual Row, 600.00mm Length, 8 Circuits, Black
Assembly Configuration	Dual Ended Connectors
Connector to Connector	N/A
Product Name	Milli-Grid
Type	Discrete Wire Assembly
UPC	195842350847

Electrical

Current - Maximum per Contact	2.0A
Voltage - Maximum	125V AC (RMS)/DC

Physical

Cable Length	600.00mm
Circuits (Loaded)	8
Circuits (maximum)	8
Color - Resin	Black
Gender	Female-Female
Lock to Mating Part	Yes
Material - Metal	Copper Alloy

Material - Plating Mating	Matte Tin
Material - Resin	Polyester
Net Weight	11.911/g
Number of Rows	2
Packaging Type	Bag
Pitch - Mating Interface	2.00mm
Single Ended	No
Termination Interface Style	Crimp or Compression
Wire/Cable Type	UL 10002
Wire Size (AWG)	24

This document was generated on Sep 24, 2025