



Part Number : [26503092](#)
Product Description : KK 396 Breakaway Header,
Vertical, 9 Circuits, Circuit 7 Voided, Matte Tin (Sn)
Plating, Pin Length 19.00mm (.750")
Series Number : 41661
Status : Active
Product Category : PCB Headers and Receptacles
Engineering Part Number : A-41661-A09A197-7



Documents and Resources

Drawings

- [026503092 sd.pdf](#)
- [PK-41661-001-001.pdf](#)
- [STEP AP242](#)
- [SOLIDWORKS](#)
- [Creo](#)
- [Symbol and Footprint \(Multi-Format\)](#)
- [SYM-26-48-1091-001.zip](#)

Specifications

- [PS-08-50-001.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	Not Reviewed per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Reviewed per IEC 61249-2-21
REACH SVHC	Not Reviewed per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Not Reviewed per EU 2015/863

[Compliance Statements](#)

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	PCB Headers and Receptacles
Series	41661
Description	KK 396 Breakaway Header, Vertical, 9 Circuits, Circuit 7 Voided, Matte Tin (Sn) Plating, Pin Length 19.00mm (.750")
Application	Board-to-Board, Signal, Wire-to-Board
Component Type	PCB Header
Product Name	KK 396
UPC	800754908092

Agency

CSA	LR19980
UL	E29179

Electrical

Current - Maximum per Contact	4.5A
Voltage - Maximum	250V

Physical

Breakaway	Yes
Circuits (Loaded)	8
Circuits (maximum)	9
Color - Resin	Black
Durability (mating cycles max)	25
First Mate / Last Break	No
Flammability	94V-0
Glow-Wire Capable	No
Guide to Mating Part	No
Keying to Mating Part	None
Lock to Mating Part	None
Material - Metal	Brass
Material - Plating Mating	Matte Tin
Material - Plating Termination	Matte Tin
Material - Resin	Polyester
Net Weight	2.646/g
Number of Rows	1
Orientation	Vertical
Packaging Type	Bag
PCB Locator	No
PCB Retention	None
PCB Thickness - Recommended	1.60mm
PC Tail Length	4.37mm
Pitch - Mating Interface	3.96mm
Pitch - Termination Interface	3.96mm
Plating min - Mating	1.524µm
Plating min - Termination	1.524µm
Polarized to Mating Part	No
Polarized to PCB	No
Shrouded	No
Stackable	Yes
Temperature Range - Operating	See Product Specification
Termination Interface Style	Through Hole

Solder Process Data

Max-Duration	5
Lead-Free Process Capability	WAVE
Max-Cycle	1
Max-Temp	235

Mates With / Use With

Mates with Part(s)

Description	Part Number
KK 3.96mm Single Row Crimp Housings	<u>2139</u>
KK 3.96mm Single Row Crimp Housings	<u>3069</u>
KK 3.96mm Crimp Housings	<u>41695</u>
KK 396 PC Board Connector	<u>41815</u>
KK 3.96mm Pitch Single Row Crimp Housings	<u>6442</u>

Application Tooling

This document was generated on Mar 01, 2026