


Part Number : [354216802](#)

Product Description : Tab Crimp Terminal 35421, AVS

Series Number : 35421

Status : Obsolete

Product Category : Crimp Terminals



Documents & Resources

Specifications

[PS-35282-001-001.pdf](#)

[PS-35385-001-001.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Compliant with Exemption 44; 34
China RoHS	Not Relevant
EU ELV	Compliant per 2000/53/EC
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2024)6225-DC (07 Nov 2024)
EU RoHS	Compliant per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

Part Details

General

Status	Obsolete
Category	Crimp Terminals
Series	35421
Description	Tab Crimp Terminal 35421, AVS
Application	Power, Wire-to-Wire
Product Name	N/A
UPC	800753943131

Physical

Gender	Female
Material - Metal	High Performance Alloy (HPA)
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Net Weight	0.306/g
Packaging Type	Reel
Plating min - Mating	0.813µm
Plating min - Termination	0.813µm
Termination Interface Style	Crimp or Compression
Wire Insulation Diameter	2.60mm max.
Wire Size (AWG)	16, 18
Wire Size mm ²	N/A

Solder Process Data

Max-Duration	10
Lead-Free Process Capability	N/A
Max-Cycle	3
Max-Temp	260

Mates With / Use With

Mates with Part(s)

Description	Part Number
Tab Terminals	<u>35420</u>

This document was generated on Oct 02, 2025

Obsolete