

10 9 8 7 6 5 4 3 2 1

注記:
NOTES:

1. 材質

MATERIAL

ハウジング : 液晶ポリマー (LCP)、ガラス充填、UL94V-0、白色

HOUSING : LIQUID CRYSTAL POLYMER (LCP), GLASS FILLED, UL94V-0, WHITE

ターミナル : りん青銅

銅めっき : 1.0μm以上

下地 : ニッケルめっき 1.0μm以上

TERMINAL : PHOSPHOR BRONZE

TIN PLATING : 1.0 MICROMETER MINIMUM

UNDERPLATE : NICKEL 1.0 MICROMETER MINIMUM

ネイル : りん青銅

銅めっき : 1.0μm以上

下地 : ニッケルめっき 1.0μm以上

NAIL : PHOSPHOR BRONZE

TIN PLATING : 1.0 MICROMETER MINIMUM

UNDERPLATE : NICKEL 1.0 MICROMETER MINIMUM

2. 嵌合相手 : 503469-****又は503473-****

MATE WITH : 503469-**** OR 503473-****

3. 端子テール部及びネイルの平坦度は0.1以下

TAIL AND NAIL COPLANARITY TO BE 0.1 MAXIMUM.

4. 端子テール部及びネイルに銅めっきを使用しているため、外観に摺動痕が付く場合があります。

THE WOUND OF FRICTION MIGHT ADHERE TO EXTERNALS

BECAUSE THE TIN PLATING IS USED FOR THE TAIL AND NAIL.

5. 本製品のプラスチック部に黒点等が確認される場合や色合いが異なる場合がありますが、製品性能に影響はありません。

THERE IS NO INFLUENCE IN THE PRODUCT PERFORMANCE THOUGH

THE BLACK SPOT ETC. MIGHT BE CONFIRMED TO THE PLASTIC PART







OF THIS PRODUCT AND THE SHADE MIGHT BE DIFFERENT.

6. エンボス極包品の詳細はSD-503471-004を参照願います。

REFER TO THE SD-503471-004 FOR EMBOSSED TAPE PACKAGING.

7. ELV及びRoHS適合品

ELV AND RoHS COMPLIANT.



基板パターンレイアウト (参考)
P.C.B. PATTERN LAYOUT (REFERENCE)
(SCALE : 5-1)

503471-0290	2
EMBOSSD TAPE PACKAGE	CIRCUIT 極数
オーダー番号 ORDER No.	
コネクタシリーズ番号 CONNECTOR SERIES No.	503471-**-09

RELEASED EC NO: J2013-1020 DRAWN:THANYU CHK'D:KASAKAWA APPR:YOITO	DESCRIPTION	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE MM ONLY		SCALE 10:1	DESIGN UNITS METRIC	THIRD ANGLE PROJECTION		
		10 UNDER	± 0.2	DRAWN BY THANYU	DATE 2013/03/18	TITLE 3.7 MULTIPLE CONN. REC. HS'G ASS'Y LOW-HALOGEN molex				
		10 OVER 30 UNDER	± 0.25	CHECKED BY KASAKAWA	DATE 2013/03/19					
		30 OVER	± 0.3	APPROVED BY YOITO	DATE 2013/03/22					
		ANGULAR ±1 °		MATERIAL NO.		DOCUMENT NO.		SHEET NO.		
	DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		SEE CHART		SD-503471-003		1 OF 2			
REV	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION									

9 8 7 6 5 4 3 2

10

9

8

7

6

5

4

3

2

1

F

E



D

C



B

A

<嵌合状態図 (参考)> 503471-****/503469-****
<MATED CONNECTOR (REFERENCE)>
(503471-****/503469-****)



<嵌合状態図 (参考)> 503471-****/503473-****
<MATED CONNECTOR (REFERENCE)>
(503471-****/503473-****)



F

E

D

C

B

A

9

8

7

6

5

4

3

2

RELEASED EC NO: J2013-1020 DRAWN: THANYU CHKD: KASAKAWA APPR: YOITO O	DESCRIPTION	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE MM ONLY		SCALE 5:1	DESIGN UNITS METRIC	THIRD ANGLE PROJECTION			
		10 UNDER	± 0.2	DRAWN BY THANYU	DATE 2013/03/18	TITLE 3.7 MULTIPLE CONN. REC. HS'G ASS'Y LOW-HALOGEN					
		10 OVER 30 UNDER	± 0.25	CHECKED BY KASAKAWA	DATE 2013/03/19						
		30 OVER	± 0.3	APPROVED BY YOITO	DATE 2013/03/22	DOCUMENT NO. SD-503471-003					
		ANGULAR ±1 °		MATERIAL NO.							SHEET NO. 2 OF 2
	DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		SEE CHART		SD-503471-003						
	REV			SIZE A3	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION						