



Part Number : [505988110](#)
Product Description : CP-6.5 Wire-to-Wire Crimp
Terminal, Female, 24-20 AWG, Bag
Series Number : 50598
Status : Active
Product Category : Crimp Terminals
Packaging Alternative : [505988010](#) (Reel)



Documents and Resources

Drawings

- [505988110 sd.pdf](#)
- [505988010-PK-000.pdf](#)
- [STEP AP242](#)
- [SOLIDWORKS](#)
- [Creo](#)

Specifications

- [2034380001-PS-000.pdf](#)
- [2034380001-TS-000.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Compliant with Exemption 44; 34
China RoHS	 per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Compliant per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC

- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Crimp Terminals
Series	50598
Description	CP-6.5 Wire-to-Wire Crimp Terminal, Female, 24-20 AWG, Bag
Application	Power, Wire-to-Wire
Comments	See Product Specification for maximum current rating by circuit size and wire AWG
Product Name	CP-6.5
UPC	193264088928

Electrical

Current - Maximum per Contact	12.5A
Voltage - Maximum	600V AC (RMS)/DC

Physical

Durability (mating cycles max)	30
Gender	Female
Material - Metal	Copper Alloy
Material - Plating Mating	Tin
Material - Plating Termination	Tin

Net Weight	246.300/mg
Packaging Type	Bag
Termination Interface Style	Crimp or Compression
Wire Insulation Diameter	1.25-2.35mm
Wire Size (AWG)	22, 24
Wire Size mm ²	N/A

Mates With / Use With

Use with Part(s)

Description	Part Number
CP-6.5 Dual Row Receptacle Housings	<u>151207</u>

Application Tooling

Global

Description	Part Number
Hand Crimp Tool for CP 6.5 Wire-to-Wire Male Terminals, 24-22 AWG	<u>2002189500</u>