


Part Number : [532617006](#)

Product Description : 1.25mm Pitch, PicoBlade PCB Header, Single Row, Right-Angle, Surface Mount, 0.38µm Gold (Au) Plating, Friction Lock, 6 Circuits, Natural, Tape and Reel

Series Number : 53261

Status : Obsolete

Product Category : PCB Headers and Receptacles



Documents & Resources

Drawings

[532617006 sd.pdf](#)

[Symbol and Footprint \(Multi-Format\)](#)

Specifications


[510210000-AS-000.pdf](#)

[510210001-PS-000.pdf](#)

[510211001-PS-000.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Compliant with Exemption 44; 33
China RoHS	 per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2024)6225-DC (07 Nov 2024)
EU RoHS	Compliant per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Obsolete
Category	PCB Headers and Receptacles
Series	53261
Description	1.25mm Pitch, PicoBlade PCB Header, Single Row, Right-Angle, Surface Mount, 0.38µm Gold (Au) Plating, Friction Lock, 6 Circuits, Natural, Tape and Reel
Application	Signal, Wire-to-Board
Component Type	PCB Header
Product Name	PicoBlade
UPC	191128467643

Agency

UL	E29179
----	--------

Electrical

Current - Maximum per Contact	1.0A
Voltage - Maximum	125V AC (RMS)/DC

Physical

Breakaway	No
Circuits (Loaded)	6
Circuits (maximum)	6

Color - Resin	Natural
Durability (mating cycles max)	30
First Mate / Last Break	No
Flammability	94V-0
Glow-Wire Capable	No
Guide to Mating Part	Yes
Keying to Mating Part	None
Lock to Mating Part	Yes
Mated Height	3.40mm
Material - Metal	Phosphor Bronze
Material - Plating Mating	Gold
Material - Plating Termination	Matte Tin
Material - Resin	Polyamide
Net Weight	198.698/mg
Number of Rows	1
Orientation	Right Angle
Packaging Type	Embossed Tape on Reel
PCB Locator	No
PCB Retention	Yes
Pitch - Mating Interface	1.25mm
Plating min - Mating	0.380µm
Plating min - Termination	1.000µm
Shrouded	Fully
Stackable	No
Temperature Range - Operating	-40° to +105°C
Termination Interface Style	Surface Mount

Mates With / Use With

Mates with Part(s)

Description	Part Number
PicoBlade Single Row Receptacle Housings	<u>51021</u>