




**Part Number :** [5054730810](#)

**Product Description :** SlimStack Board-to-Board Receptacle, 0.40mm Pitch, Battery Series, 0.60mm Mated Height, 2.00mm Mated Width, 8 Circuits, 10.0A

**Series Number :** 505473

**Status :** Not Recommended For New Design

**Product Category :** Board-to-Board Connectors



---

## Documents & Resources

### Drawings

[5054730810\\_sd.pdf](#)

### 3D Models and Design Files

[STEP AP242](#)

[SOLIDWORKS](#)

[Creo](#)

[Symbol and Footprint \(Multi-Format\)](#)

[5054730810.dxf](#)

### Specifications

[5054730000-A00.pdf](#)


[5054739200-200.pdf](#)

[5054730000-000.pdf](#)

---

## Product Environment Compliance

### Compliance

GADSL/IMDS	Compliant with Exemption 33; 44; 34
China RoHS	 per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)4165-DC (25 June 2025)
EU RoHS	Compliant per EU 2015/863

## Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

## Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

## Substances of Interest

- PFAS

## EU RoHS Certificate of Compliance

## Additional Product Compliance Information

---

## Part Details

### General

Status	Not Recommended For New Design
Category	Board-to-Board Connectors
Series	10A, Battery
Description	SlimStack Board-to-Board Receptacle, 0.40mm Pitch, Battery Series, 0.60mm Mated Height, 2.00mm Mated Width, 8 Circuits, 10.0A
Application	Board-to-Board
Comments	10A of current per circuit is applicable if the circuit is constructed by two power pins via a PWB/FPC circuit
Component Type	PCB Receptacle
Product Name	SlimStack
UPC	889056268875

### Electrical

Current - Maximum per Contact	0.5A, 5.0A*
Voltage - Maximum	50V AC (RMS)/DC

## Physical

Circuits (Loaded)	8
Circuits (maximum)	8
Color - Resin	Black
Durability (mating cycles max)	10
Glow-Wire Capable	No
Lock to Mating Part	Yes
Mated Height	0.60mm
Mated Width	2.00mm
Material - Metal	Copper Alloy
Material - Plating Mating	Gold
Material - Plating Termination	Gold
Material - Resin	Liquid Crystal Polymer
Net Weight	9.490/mg
Number of Rows	2
Orientation	Vertical
Packaging Type	Embossed Tape on Reel
PCB Locator	No
PCB Retention	Yes
Pitch - Mating Interface	0.40mm
Pitch - Termination Interface	0.40mm
Plating min - Mating	0.100µm
Plating min - Termination	0.050µm
Polarized to Mating Part	No
Polarized to PCB	No
(p)ower-(s)ignal Configuration	4p - 4s
Temperature Range - Operating	-40° to +85°C
Termination Interface Style	Surface Mount

---

## Mates With / Use With

### Mates with Part(s)

Description	Part Number
0.40mm Pitch SlimStack Board-to-Board Plugs	<u>505476</u>

