



**Part Number :** [732870323](#)

**Product Description :** 2.92mm Attenuator, Plug to Jack, Straight, 40 GHz, 2 Watt, 6 dB, with Hex

**Series Number :** 73287

**Status :** Active

**Product Category :** RF / Coaxial Connectors



---

## Documents & Resources

### Drawings

[732870323\\_sd.pdf](#)

[STEP AP242](#)

[SOLIDWORKS](#)

[Creo](#)

---

## Product Environment Compliance

### Compliance

GADSL/IMDS	Not Relevant
China RoHS	Not Reviewed per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Reviewed per IEC 61249-2-21
REACH SVHC	Not Reviewed per D(2025)4165-DC (25 June 2025)
EU RoHS	Not Reviewed per EU 2015/863

### Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

### Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

## Substances of Interest

- PFAS

## EU RoHS Certificate of Compliance

## Additional Product Compliance Information

---

### Part Details

#### General

Status	Active
Category	RF / Coaxial Connectors
Series	73287
Description	2.92mm Attenuator, Plug to Jack, Straight, 40 GHz, 2 Watt, 6 dB, with Hex
Application	RF
Keyword	Attenuators, Attenuator
Product Name	2.92mm,Attenuator
Style	Fixed Coaxial Attenuator
Type	Subminiature
UPC	198282631323

#### Electrical

Average Power Max (Watts)	2
Attenuation Level (dB)	6
Frequency	40 GHz
Impedance	50Ω
VSWR (max)	1.40:1

#### Physical

Body Style	With Hex
Cable Attachment	N/A
Gender	Plug/Jack
Keying to Mating Part	N/A
Orientation	Straight
Packaging Type	Bag
Panel Mount	No

Panel Mount Method	N/A
PCB Mounting	N/A
Reverse Polar	No
Wire/Cable Type	N/A

---

This document was generated on Oct 02, 2025