




Part Number : [751982501](#)
Product Description : VHDM L-Series Single-Ended Backplane Header, 2.00mm Pitch, Guide Pin Signal Module, Pin End Version, 8 Rows, 200 Circuits, 25 Columns, Pin Length 4.75m, Lead-Free
Series Number : 75198
Status : Active
Product Category : Backplane Connectors



Documents & Resources

Drawings
[751982501 sd.pdf](#)
[PK-74061-003-001.pdf](#)

Specifications
[PS-74031-999-001.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	 per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2024)6225-DC (07 Nov 2024)
EU RoHS	Compliant per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D

- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Backplane Connectors
Series	75198
Description	VHDM L-Series Single-Ended Backplane Header, 2.00mm Pitch, Guide Pin Signal Module, Pin End Version, 8 Rows, 200 Circuits, 25 Columns, Pin Length 4.75m, Lead-Free
Application	Backplane
Comments	No Keying Position
Component Type	PCB Header
Product Name	VHDM L-Series
UPC	822348810369

Agency

UL	E29179
----	--------

Electrical

Current - Maximum per Contact	3.0A
Data Rate	622.0 Mbps
Shielded	No
Voltage - Maximum	120V AC (RMS)/DC

Physical

Circuits (Loaded)	200
-------------------	-----

Circuits (maximum)	200
Color - Resin	Black
Durability (mating cycles max)	200
First Mate / Last Break	No
Flammability	94V-0
Guide to Mating Part	Yes
Keying to Mating Part	None
Material - Metal	High Performance Alloy (HPA), Stainless Steel
Material - Plating Mating	Gold
Material - Plating Termination	Tin
Material - Resin	High Temperature Thermoplastic
Net Weight	10.694/g
Number of Columns	25
Number of Pairs	Open Pin Field
Number of Rows	8
Orientation	Vertical
Packaging Type	Tube
PCB Locator	No
PCB Retention	Yes
PCB Thickness - Recommended	1.80mm
PC Tail Length	2.50mm
Pitch - Mating Interface	2.00mm
Pitch - Termination Interface	2.00mm
Plating min - Mating	0.762µm
Plating min - Termination	0.762µm
Polarized to PCB	No
Temperature Range - Operating	105°C
Termination Interface Style	Through Hole - Compliant Pin

Mates With / Use With

Use with Part(s)

Description	Part Number
Use With	Daughtercard Modules

Application Tooling

Global

Description	Part Number
Signal Pin Inserter Repair Tool	<u>622015700</u>