



Part Number : [797581148](#)

Product Description : Pre-Crimped Lead Micro-Lock Plus 1.25 Female-to-Micro-Lock Plus 1.25 Female, Matte Tin (Sn) Plating, 150.00mm Length, 26 AWG, Black

Series Number : 79758

Status : Active

Product Category : Power and Signal Cable Assemblies



Documents and Resources

Drawings

[797581148 sd.pdf](#)

[STEP AP242](#)

[SOLIDWORKS](#)

[Creo](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	 per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Compliant per EU 2015/863

[Compliance Statements](#)

- EU RoHS
- REACH SVHC
- Low-Halogen

[Industry Documents](#)

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Power and Signal Cable Assemblies
Series	79758
Description	Pre-Crimped Lead Micro-Lock Plus 1.25 Female-to-Micro-Lock Plus 1.25 Female, Matte Tin (Sn) Plating, 150.00mm Length, 26 AWG, Black
Application	Wire-to-Board
Assembly Configuration	Pre-crimped Lead Only
Connector to Connector	Micro-Lock Plus Terminal-to-Micro-Lock Plus Terminal
Keyword	Micro-Lock Plus 1.25, Pre-Crimped Leads
Product Name	Micro-Lock Plus
UPC	191130056477

Electrical

Current - Maximum per Contact	1.5A
Voltage - Maximum	50V AC (RMS)/DC

Physical

Cable Length	150.00mm
Circuits (Loaded)	1

Circuits (maximum)	1
Color - Resin	Black
Gender	Female-Female
Material - Metal	Copper Alloy
Material - Plating Mating	Matte Tin
Material - Plating Termination	Tin
Net Weight	0.370/g
Number of Rows	1
Packaging Type	Bag
Pitch - Mating Interface	1.25mm
Plating min - Mating	0.700µm
Single Ended	No
Termination Interface Style	Crimp or Compression
Wire/Cable Type	UL 1061
Wire Size (AWG)	26

Mates With / Use With

Use with Part(s)

Description	Part Number
1.25mm Pitch, Micro-Lock Plus Dual Row Receptacle Housings	<u>505432</u>
1.25mm Pitch, Micro-Lock Plus Single Row Receptacle Housings	<u>505565</u>