




Part Number : [732860210](#)

Product Description : Bolt-in EMI Filter Plate,
Standard Density, 2x6, Straight, 100 pF C Feedthrough,
39.62mm Plate Length

Series Number : 73286

Status : Active

Product Category : EMI Filter Plates



Documents & Resources

Drawings

[732860210 sd.pdf](#)

[STEP AP242](#)

[SOLIDWORKS](#)

[Creo](#)

[Symbol and Footprint \(Multi-Format\)](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	Not Reviewed per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Reviewed per IEC 61249-2-21
REACH SVHC	Not Reviewed per D(2025)4165-DC (25 June 2025)
EU RoHS	Not Reviewed per EU 2015/863

[Compliance Statements](#)

- EU RoHS
- REACH SVHC
- Low-Halogen

[Industry Documents](#)

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration

- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	EMI Filter Plates
Series	73286
Description	Bolt-in EMI Filter Plate, Standard Density, 2x6, Straight, 100 pF C Feedthrough, 39.62mm Plate Length
Application	RF
Product Name	Bolt-in EMI Filter Plates
Type	Bolt-in Standard Density
UPC	198282678564

Electrical

Current - Maximum per Contact	5.0A
Capacitance Value	100 pF
Capacitance Tolerance	± 25%
3 dB Cut-off Frequency Max. (MHz)	50.3
Dielectric Withstanding Voltage (V)	250
EMI Filter Circuits	Capacitive
Minimum Insertion Loss (dB) - 1 GHz	19
Minimum Insertion Loss (dB) - 100 MHz	1
Minimum Insertion Loss (dB) - 200 MHz	6
Minimum Insertion Loss (dB) - 500 MHz	13
Voltage - Maximum	100V DC

Physical

Circuits (Loaded)	12
Length	39.62mm
Material - Contact	Copper Alloy
Material - Plating Mating	Gold
Material - Plating Termination	Gold
Number of Rows	2
Number of Lines per Row	6
Orientation	Straight
Packaging Type	Tray
Pitch - Mating Interface	2.54mm
Pitch - Termination Interface	2.54mm