



Part Number : [873819015](#)

Product Description : 2.00mm Pitch Milli-Grid
Receptacle, Surface Mount, Top Entry, 0.76µm Gold
(Au) Plating, with Cover, with Locating Pegs, 30 Circuits,
Lead-Free, Tape and Reel

Series Number : 87381

Status : Active

Product Category : PCB Headers and Receptacles



Documents and Resources

Drawings

- [873819015 sd.pdf](#)
- [PK-87368-0001-001.pdf](#)
- [873810001-PK-000.pdf](#)

3D Models and Design Files

- [STEP AP242](#)
- [SOLIDWORKS](#)
- [Creo](#)
- [Symbol and Footprint \(Multi-Format\)](#)

Specifications

- [503940001-AS-000.pdf](#)
- [PS-87380-002-001.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Compliant with Exemption 44
China RoHS	 per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)7771-DC (04 Feb 2026)

EU RoHS	Compliant per EU 2015/863
---------	---------------------------

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	PCB Headers and Receptacles
Series	87381
Description	2.00mm Pitch Milli-Grid Receptacle, Surface Mount, Top Entry, 0.76µm Gold (Au) Plating, with Cover, with Locating Pegs, 30 Circuits, Lead-Free, Tape and Reel
Application	Board-to-Board
Component Type	PCB Receptacle
Product Name	Milli-Grid
UPC	822348484218

Agency

CSA	LR19980
UL	E29179

Electrical

Current - Maximum per Contact	1.9A
-------------------------------	------

Voltage - Maximum	125V
-------------------	------

Physical

Circuits (Loaded)	30
Circuits (maximum)	30
Color - Resin	Black
Durability (mating cycles max)	25
First Mate / Last Break	No
Flammability	94V-0
Gender	Female
Glow-Wire Capable	No
Lock to Mating Part	No
Material - Metal	Phosphor Bronze
Material - Plating Mating	Gold
Material - Plating Termination	Tin
Material - Resin	High Temperature Thermoplastic
Net Weight	0.777/g
Number of Rows	2
Orientation	Vertical
Packaging Type	Embossed Tape on Reel
PCB Locator	Yes
PCB Retention	Yes
Pitch - Mating Interface	2.00mm
Pitch - Termination Interface	2.00mm
Plating min - Mating	0.762µm
Plating min - Termination	1.270µm
Polarized to PCB	No
Robotic Placement	Pick and Place Cap
Stackable	Yes
Temperature Range - Operating	-55° to +105°C
Termination Interface Style	Surface Mount

Mates With / Use With

Mates with Part(s)

Description	Part Number
Milli-Grid Vertical Through Hole Headers	<u>87758</u>
Milli-Grid Vertical Surface Mount Headers	<u>87759</u>
Milli-Grid Right-Angle Through Hole Headers	<u>87760</u>
Milli-Grid Vertical, Dual Row, Through Hole Headers	<u>87831</u>
Milli-Grid Vertical, Dual Row, Surface Mount Headers	<u>87832</u>