



Part Number : [760915003](#)

Product Description : Small Form-factor Pluggable Plus (SFP+) Stacked 2-by-2 Multi-Port Connector with 2 Outer Lightpipe Ports, Elastomeric Gasket, 80 Circuits, Tin (Sn) Tails

Series Number : 76091

Status : Obsolete

Product Category : High-Speed I/O Connectors



Documents and Resources

Drawings

[760915003 sd.pdf](#)

[760915003 stp.zip](#)

[EE-76090-001-001.pdf](#)

[SP-76090-001-001.zip](#)

Specifications

[AS-75310-001-001.pdf](#)

[AS-76090-001-001.pdf](#)

[PK-75714-001-001.pdf](#)

[PS-75310-001-001.pdf](#)

[TS-76092-999-001.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	 per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2022)4187-DC (10 June 2022)
EU RoHS	Compliant per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Obsolete
Category	High-Speed I/O Connectors
Series	76091
Description	Small Form-factor Pluggable Plus (SFP+) Stacked 2-by-2 Multi-Port Connector with 2 Outer Lightpipe Ports, Elastomeric Gasket, 80 Circuits, Tin (Sn) Tails
Application	Module-to-Board
Component Type	Receptacle
Product Name	SFP Plus
Type	N/A
UPC	883906495046

Agency

CSA	LR19980
UL	E29179

Electrical

Current - Maximum per Contact	0.5A
Grounding to Panel	None

Shielded	Yes
Shield Type	EMI Gasket
Voltage - Maximum	120V AC (RMS)/DC

Physical

Boot Color	N/A
Circuits Detail	160
Circuits (Loaded)	80
Circuits (maximum)	80
Color - Resin	Black, Clear (Blue Tint)
Durability (mating cycles max)	100
Flammability	94V-0
Gender	Female
Keying to Mating Part	None
Lock to Mating Part	Yes
Material - Metal	High Performance Alloy (HPA)
Material - Plating Mating	Gold
Material - Plating Termination	Tin
Material - Resin	High Temperature Thermoplastic, Polycarbonate
Net Weight	50.018/g
Number of Rows	2
Orientation	Right Angle
Packaging Type	Tray
Panel Mount	No
PCB Locator	Yes
PCB Retention	Yes
PCB Thickness - Recommended	1.57mm
PC Tail Length	2.07mm
Pitch - Mating Interface	0.80mm
Pitch - Termination Interface	0.80mm
Plating min - Mating	0.762μm
Plating min - Termination	0.762μm
Polarized to Mating Part	Yes
Polarized to PCB	Yes

Temperature Range - Operating	-40° to +85°C
Termination Interface Style	Through Hole - Compliant Pin
Waterproof / Dustproof	No

Solder Process Data

Lead-Free Process Capability	N/A
------------------------------	-----

Application Tooling

This document was generated on Feb 27, 2026

Obsolete