



Part Number : [768551828](#)
Product Description : Impact 100 Ohm 3 Pair
Vertical Orthogonal Header Unguided, Dual Endwall, 8
Columns, 72 Circuits, Pin Length 5.50mm, Plated
Through Hole Dimension 0.39mm, Lead-Free
Series Number : 76855
Status : Active
Product Category : Backplane Connectors



Documents and Resources

Drawings

[768551828 sd.pdf](#)
[PK-70873-7705-001.pdf](#)

3D Models and Design Files

[STEP AP242](#)
[SOLIDWORKS](#)
[Creo](#)
[SYM-76855-1828-001.zip](#)

Specifications

[AS-76060-9999-001.pdf](#)
[AS-76850-990-001.pdf](#)
[PS-45499-002-001.pdf](#)
[PS-76060-999-001.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	 per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)7771-DC (04 Feb 2026)

EU RoHS	Compliant per EU 2015/863
---------	---------------------------

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Backplane Connectors
Series	76855
Description	Impact 100 Ohm 3 Pair Vertical Orthogonal Header Unguided, Dual Endwall, 8 Columns, 72 Circuits, Pin Length 5.50mm, Plated Through Hole Dimension 0.39mm, Lead-Free
Application	Orthogonal Midplane
Component Type	PCB Header
Product Name	Impact
UPC	884982189751

Agency

UL	E29179
----	--------

Electrical

Current - Maximum per Contact	0.75A
-------------------------------	-------

Data Rate	25.0 Gbps
Impedance	100Ω
Shielded	No
Shield Type	N/A
Voltage - Maximum	30V AC (RMS)/DC

Physical

Circuits (Loaded)	72
Circuits (maximum)	72
Color - Resin	Black
Durability (mating cycles max)	200
First Mate / Last Break	No
Flammability	94V-0
Guide to Mating Part	No
Keying to Mating Part	None
Material - Metal	High Performance Alloy (HPA)
Material - Plating Mating	Gold
Material - Plating Termination	Tin
Material - Resin	High Temperature Thermoplastic
Net Weight	2.578/g
Number of Columns	8
Number of Pairs	3
Number of Rows	9
Orientation	Vertical
Packaging Type	Tray
PCB Locator	No
PCB Retention	None
PCB Thickness - Recommended	3.00mm
PC Tail Length	1.40mm
Pitch - Mating Interface	1.90mm, 2.15mm
Pitch - Termination Interface	1.90mm, 2.15mm
Plating min - Mating	0.762μm
Polarized to PCB	No
Stackable	No
Temperature Range - Operating	-55° to +85°C

Termination Interface Style	Through Hole - Compliant Pin
-----------------------------	------------------------------

Solder Process Data

Lead-Free Process Capability	N/A
------------------------------	-----

Mates With / Use With

Mates with Part(s)

Description	Part Number
Impact 100 Ohm 3 Pair Right-Angle Orthogonal Daughtercards	<u>76860</u>

Application Tooling

This document was generated on Feb 26, 2026